### **SIEMENS**

#### ACVATIX™

## 2-port and 3-port valves, externally threaded, PN16

VVG44.., VXG44...




In small and medium-sized heating, ventilating and air conditioning systems as a control valve for mixing and diverting functions or as a shutoff valve. For closed circuits only.

- Housing made of bronze CC499K
- DN 15...40
- k<sub>vs</sub> 0.25...25 m<sup>3</sup>/h
- Flat sealing, externally threaded connections G..B, as per ISO 228-1
- Siemens can deliver fitting sets ALG.. with threaded connection and ALS.. with welded connection
- Manual adjustment by means of mounted knob
- Can be equipped with motorized SAS.. actuators

#### Design


Valve cross-section:

# Guided parabolic plug, integrated in the valve stem. The seat is pressed to the valve body with the aid of special gland material. Caution: The 2-port seat valve does not become a three-port valve by removing the cover plate!



#### **Sizing**

Flow diagram:



Δp<sub>max</sub> = Maximum permissible differential pressure across the valve (VXG44..: mixing port: Ports A-AB, B-AB, diverting: Ports AB-A, AB-B), valid for the entire actuating range valve-actuator unit


 $\Delta p_{v100}$  = Differential pressure across the fully open valve and the valve's control path (VXG44... A - AB, B - AB) at a volume flow V<sub>100</sub>


¥ 100 = Volume flow through the fully open valve (H₁00)

100 kPa = 1 bar ≈ 10 mWS

 $1 \text{ m}^3/\text{h} = 0.278 \text{ l/s water at } 20 ^{\circ}\text{C}$ 


#### Valve flow characteristic





#### Cavitation

Cavitation increases wear and tear on the parabolic plug and seat and results in unwanted noise. Cavitation can be prevented by not exceeding the differential pressures as per the flow diagram and maintaining the static pressures depicted below.



Δp<sub>max</sub> = Differential pressure at a nearly closed valve to largely avoid

cavitation

 $p_1$  = Static pressure and the valve inlet

 $P_3$  = Static pressure and the valve outlet

M Pump

J Water temperature

Example with hot water:

Pressure p<sub>1</sub> at valve inlet: 500 kPa (5 bar)

Water temperature: 120 °C

The above diagram clearly indicates that the maximum permissible differential pressure is

 $\Delta p_{\text{max}} \rightarrow 200 \text{ kPa}$  (2 bar) at a nearly closed valve.


Note on chilled water applications

To prevent cavitation in chilled water circuits, sufficient counter pressure must be supplied to the valve output, e.g. using an additional butterfly valve downstream of the valve. Maximum permissible differential pressure over the valve: See 80 °C curve in the above diagram.

 $\Delta$ pmax

#### Operating pressure and operating temperature

Liquids:



Operating pressure and medium temperature per ISO 7005 (Observe all local and applicable laws).

#### Type summary

Туре	DN	K <sub>vs</sub>	S <sub>v</sub>
		[m³/h]	
VVG44.15-0.25 VXG44.15-0.25	15	0.25	>50
VVG44.15-0.4 VXG44.15-0.4		0.4	_
VVG44.15-0.63 VXG44.15-0.63		0.63	
VVG44.15-1 VXG44.15-1		1	
VVG44.15-1.6 VXG44.15-1.6		1.6	>100
VVG44.15-2.5 VXG44.15-2.5		2.5	-
VVG44.15-4 VXG44.15-4		4	_
VVG44.20-6.3 VXG44.20-6.3	20	6.3	
VVG44.25-10 VXG44.25-10	25	10	
VVG44.32-16 VXG44.32-16	32	16	
VVG44.40-25 VXG44.40-25	40	25	

DN = Nominal size

k<sub>vs</sub> = Flow nominal value for cold water (5...30 °C) through a fully opened valve (H100), at a differential pressure of 100 kPa (1 bar)

 $S_v$  = Rangeability  $k_{vs} / k_{vr}$ 

 $k_{vr}$  = Smallest  $k_v$  value at which the characteristic curve tolerance is still maintained, at a differential pressure of 100 kPa (1 bar)

Siemens

#### **Fittings**

Туре	Stock number	Description
ALG2	BPZ:ALG2	2 piece fittings set for 2-port valves, existing of 2 cap nuts, 2 insert nuts,
ALG2B	S55846-Z1	and 2 flat seals.  ALG2B are fittings made of brass for media temperatures up to 100 °C
ALG3	BPZ:ALG3	3 piece fittings set for 3-port valves, existing of 3 cap nuts, 3 insert nuts,
ALG3B	S55846-Z1	and 3 flat seals.  ALG3B are fittings made of brass for media temperatures up to 100 °C
ALS2	BPZ:ALS	2 piece on pipe fittings set with welded connection for 2-port valves, existing of 2 cap nuts, 2 insert nuts, and 2 flat seals

# **Filter** Installed upstream of the valve:

Туре	Stock number	Description	DN	Mesh width [mm]
ALX15	S55845-Z174	Filter with internal threading	15	0.5
ALX20	S55845-Z175	Filter with internal threading	20	0.8
ALX25	S55845-Z176	Filter with internal threading	25	0.8
ALX32	S55845-Z177	Filter with internal threading	32	0.8
ALX40	S55845-Z178	Filter with internal threading	40	0.8
ALX50	S55845-Z179	Filter with internal threading	50	0.8

#### **Equipment combinations**

Valves	SAS ac	ctuators
	Dp <sub>max</sub> Mixing 1)	Dp <sub>s</sub> Diverting 1)
	[kPa]	[kPa]
VVG44.15-0.25	400	1600
VVG44.15-0.4		
VVG44.15-0.63		
VVG44.15-1		725
VVG44.15-1.6		
VVG44.15-2.5		400
VVG44.15-4		
VVG44.20-6.3		750
VVG44.25-10		400
VVG44.32-16	250	250
VVG44.40-25	125	125
VXG44.15-0.25	400	100
VXG44.15-0.4		
VXG44.15-0.63		
VXG44.15-1		
VXG44.15-1.6		
VXG44.15-2.5		
VXG44.15-4		
VXG44.20-6.3		
VXG44.25-10		75
VXG44.32-16	250	50
VXG44.40-25	125	35

<sup>1) =</sup> Three-port valves only: If noise is permitted, the same values apply as for a mixing valve

Valves	Fittings set				
		Threaded connection			
	Malleable cast iron	Brass 1)		Steel	
	Type / Item NO.	Туре	Item NO.	Type / Item NO.	
VVG44.15-0.25	ALG152	ALG152B	S55846-Z100	ALS202	
VVG44.15-0.4					
VVG44.15-0.63					
VVG44.15-1					
VVG44.15-1.6					
VVG44.15-2.5					
VVG44.15-4					
VVG44.20-6.3	ALG202	ALG202B	S55846-Z102	ALS252	
VVG44.25-10	ALG252	ALG252B	S55846-Z104	-	
VVG44.32-16	ALG322	ALG322B	S55846-Z106	-	
VVG44.40-25	ALG402	ALG402B	S55846-Z108	-	
VXG44.15-0.25	ALG153	ALG153B	S55846-Z101	-	
VXG44.15-0.4					
VXG44.15-0.63					
VXG44.15-1					
VXG44.15-1.6					
VXG44.15-2.5					
VXG44.15-4	1				
VXG44.20-6.3	ALG203	ALG203B	S55846-Z103	-	
VXG44.25-10	ALG253	ALG253B	S55846-Z105	-	
VXG44.32-16	ALG323	ALG323B	S55846-Z107	-	
VXG44.40-25	ALG403	ALG403B	S55846-Z109	-	

<sup>&</sup>lt;sup>1)</sup> Medium temperature: Maximal 100 °C

Δp<sub>max</sub> = Maximum permissible differential pressure over the valve control path, valid for the entire positioning range of the valve-actuator unit; if low noise operation is desired, we recommend a differential pressure of 200 kPa

 $\Delta p_s$  = Maximum permissible differential pressure (closing pressure) at which the valve-actuator unit securely closes against the pressure

#### **Actuators: Overview**

Typ3	Stock number	Operating	Position	ning	Spring	return	Data sheet
		voltage	voltage Signal Time	Time		Signal	
SAS31.00	S55158-A106	AC 230 V	3-position	120 s	-	-	N4581
SAS31.03	S55158-A107			30 s			
SAS31.50	S55158-A108			120 s	ja	< 28 s	
SAS31.53	S55158-A109			30 s	ja	< 14 s	
SAS61.03 <sup>1)</sup>	S55158-A100	AC/DC 24 V	DC 010 V	30 s	-	-	
SAS61.03U <sup>2)</sup>	S55158-A100-A100		DC 420 mA 01000 Ω				
SAS61.03/MO	S55158-A121		Modbus RTU				
SAS61.33 <sup>1)</sup>	S55158-A101		DC 010 V		ja	< 14 s	
SAS61.33U <sup>2)</sup>	S55158-A101-A100		DC 420 mA 01000 Ω				
SAS61.33U/MO	S55158-A122		Modbus RTU				
SAS61.53 <sup>1)</sup>	S55158-A102		DC 010 V DC 420 mA 01000 Ω				
SAS81.00 <sup>1)</sup>	S55158-A103	AC/DC 24 V	3-position	120 s	-	-	
SAS81.00U <sup>2)</sup>	S55158-A103-A100						
SAS81.03 <sup>1)</sup>	S55158-A104			30 s			
SAS81.03U <sup>2)</sup>	S55158-A104-A100						
SAS81.33 <sup>1)</sup>	S55158-A105				ja	< 14 s	
SAS81.33U <sup>2)</sup>	S55158-A1105-A100						

<sup>1)</sup> Approbation CE+UL

#### **Ordering**

Please indicate material, article type, order text, and quantity; example:

Material	Article type	Order text	Quantity
VVG44.25-10	VVG44.25-10	Valve.	3
ALG252B	S55846-Z104	Fitting sets	3

#### **Delivery**

Valves, rotary actuators, and mounting kits are not assembled and are delivered in individual packaging and without a minimum order size.

#### Product documentation

Related documents such as environmental declarations, CE declarations, etc., can be downloaded at the following Internet address:

http://siemens.com/bt/download

Siemens

<sup>&</sup>lt;sup>2)</sup> Approbation CE+UL, cable gland: ½" (UL514C)

#### Safety



#### **▲** DANGER

#### There is a risk to operating personnel and device when working on the unit

Failure to comply with these safety notes can result in personal injury and damage to property from pipe pressure, electrical voltage, or device in operation.

- □ Note the following when servicing a valve/actuator:
- Switch off both pump and operating voltage.
- Close shutoff valves.
- Release pressure in the pipes and allow them to cool down completely.
- Disconnect electrical connections from the terminals as needed.
- The actuator must be properly installed or manually adjusted prior to recommissioning the valve.



#### **A** CAUTION

#### National safety regulations

Failure to comply with national safety regulations may result in personal injury and property damage.

Observe national provisions and comply with the appropriate safety regulations.

#### **Engineering**

We recommend installing the valve with spring return since temperatures are lower on heating plants which increases the lifespan of the sealing gland on the stem.


A filter must be installed upstream of the valve to increase functional safety.

#### Mounting

It is easy to assemble the valve and actuator; it can be done at the construction site. No special tools or settings required.

Valve VVG44.. / VXG44.. is supplied with Mounting instructions M4364 (4 319 9564 0).

#### **Mounting position**



#### Pipe connection

Avoid leakage:

- Install fittings as per ISO 7-1.
- Do not use too much hemp or PTFE tape.
- Do not tighten pipe threading to "the very end".

#### Flow direction

Make sure that the valve is mounted in the proper flow direction. A symbol is applied to the valve body:

VVG44:	
Flow direction:	<b>→</b>

VXG44:			
Mixing A / B to AB:	A AB 44642003b	Diverting AB to A / B:	AB A 1464Z030:

#### Commissioning

The actuator must be properly mounted or manually adjusted before commissioning the valve.

VVG44		
Turn the manual adjuster clockwise:	Valve opening = Increasing flow	
Turn the manual adjuster counter clockwise:	Valve closing = Decreasing flow	

VXG44			
Turn the manual adjuster clockwise:	Through-put A – AB opens, bypass B closes		
Turn the manual adjuster counter clockwise:	Through-put A – AB closes, bypass B opens		

#### Maintenance

Valves VVG44.. and VXG44.. are maintenance free.

#### Stem sealing gland

The stem sealing gland cannot be exchanged. The entire valve must be replaced in the event of leakage. Contact your local Siemens office or branch for information.

#### **Disposal**



#### WARNING

#### Tensioned return spring

Opening the valve housing can release the tensioned return spring resulting in flying parts that may cause injury.

• Do not open the valve body.



The valve is considered electrical and electronic equipment for disposal in terms of the applicable European Directive and may not be disposed of as domestic garbage.

- Dispose of the valve through channels provided for this purpose.
- Comply with all local and currently applicable laws and regulations.

Technical data on specific applications are valid only together with Siemens products listed under "Equipment combinations". Siemens rejects any and all warranties in the event that third-party products are used.

#### Technical data

Functional data				
	VVG44	VXG44		
PN class	PN 16 per ISO 7268			
Operating pressure	Per ISO 7005 within the permissible n Technical design [→ 2]	Per ISO 7005 within the permissible media temperature as per Section Technical design [→ 2]		
Characteristic curve 0100 %	linear as per VDI / VDE 2173	linear as per VDI / VDE 2173		
Leakage rate	$00.02~\%$ of $k_{vs}$ value per DIN EN 1349	00.02 % of k <sub>vs</sub> value per DIN EN 1349 (through-put and bypass)		
Permissible media		Chilled water, hot water, water with frost temperature.  Recommendation: Water treatment per VDI 2035		
Medium temperature 1)	1120 °C			
Rangeability S <sub>v</sub>	DN 15: >50 or >100, see Section Type overview [→ 6] DN ≥20: >100			
Nominal stroke	5.5 mm			

Materials					
Housing	Bronze CC499K				
Seat in through-put	CrNi steel, bronze (worked directly into housing) or Messing				
Seat in bypass (VXG44 only)	Bronze (worked directly into housing) or brass				
Plug	CrNi steel or brass				
Stem	CrNi steel				
Sealing gland	Brass				
Gland materials	EPDM-O rings				


Dimensions / Weight					
See Dimensions [→ 14]					
Connections with external threading	GB per ISO 228-1				
Actuator fixing	G ¾"				

Standards, directives and approvals					
Pressure Equipment Directive	DGR 2014/68/EU				
Pressure accessories Fluid group 2	Range: Article 1, para. 1 Definition: Article 2, para. 5 Without CE certification as per article 3, para. 3 (generally applicable engineering practice) 2)				
EAC compliance	Eurasian compliance				
Environmental compatibility	Environmental Declaration CE1E4364en <sup>3)</sup> contains data on environmental-compatible product design and assessment (RoHS compliance, compositions, packaging, environmental benefits and disposal).				

<sup>1)</sup> With ALG..B fitting up to 100 °C

Fittings for a product where PS x DN < 1000, do not require special testing and cannot have CE labeling

<sup>&</sup>lt;sup>3)</sup> See Section Product documentation [ $\rightarrow$  10]



DN = Nominal size

H = Total height of actuator plus minimum mounting distance to wall or ceiling, for mounting, connection, operation, maintenance, etc.

H1 = Dimension from the pipe to the center to install actuator (upper edge)

H2 = Pipe center to the upper edge of the manual adjustment button, valve is in the "closed" position

Valve type	DN	В	G	L1	L2	L3	H1	H2	Н	Weight
		mm	Inch	mm	mm	mm	mm	mm	SAS	kg
VVG44.15-0.25	15	8,5	G 1B	100	50	58	45	55	>381	0.65
VVG44.15-0.4										
VVG44.15-0.63										
VVG44.15-1										
VVG44.15-1.6							49	59		0.67
VVG44.15-2.5										
VVG44.15-4		12					53	63		0.77
VVG44.20-6.3	20	9	G 11/4B			59	68	78	>396	1.0
VVG44.25-10	25	11	G 1½B	105	52.5	62.5	71	81	>399	1.48
VVG44.32-16	32		G 2B			63.5	77.5	87.5	>406	1.95
VVG44.40-25	40		G 21/4B	130	65	76	80.5	90.5	>409	2.75
VXG44.15-0.25	15	8.5	G 1B	100	50	50	45	55	>381	0.5
VXG44.15-0.4										
VXG44.15-0.63										
VXG44.15-1										
VXG44.15-1.6							49 5	59		0.59
VXG44.15-2.5										
VXG44.15-4							53	63		0.67
VXG44.20-6.3	20	9	G 11/4B				68	78	>396	0.90
VXG44.25-10	25	11	G 1½B	105	52.5	52.5	71	81	>399	1.30
VXG44.32-16	32		G 2B				77.5	87.5	>406	1.74
VXG44.40-25	40	1	G 21/4B	130	65	65	80.5	90.5	>409	2.39

#### **Fittings**

	Туре	Article no.	Туре	Article no.	For valve	G	Rp
					type	[inch]	[inch]
VVG44	ALG152	BPZ:ALG152	ALG152B	S55846-Z100	VVG44.15	G 1	Rp ⅓
4383M02	ALG202	BPZ:ALG202	ALG202B	S55846-Z102	VVG44.20	G 1¼	Rp ¾
	ALG252	BPZ:ALG252	ALG252B	S55846-Z104	VVG44.25	G 1½	Rp 1
& + - o	ALG322	BPZ:ALG322	ALG322B	S55846-Z106	VVG44.32	G 2	Rp 11/4
	ALG402	BPZ:ALG402	ALG402B	S55846-Z108	VVG44.40	G 21/4	Rp 1½
VXG44	ALG153	BPZ:ALG153	ALG153B	S55846-Z101	VXG44.15	G 1	Rp ⅓
4383M02	ALG203	BPZ:ALG203	ALG203B	S55846-Z103	VXG44.20	G 1¼	Rp ¾
	ALG253	BPZ:ALG253	ALG253B	S55846-Z105	VXG44.25	G 1½	Rp 1
\& \\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	ALG323	BPZ:ALG323	ALG323B	S55846-Z107	VXG44.32	G 2	Rp 1¼
	ALG403	BPZ:ALG403	ALG403B	S55846-Z109	VXG44.40	G 2¼	Rp 1½

- Valve side with cyclindrical threading per ISO 228-1
- Pipe side with cyclindrical threading per ISO 7-1
- ALG..B fittings up to 100 °C medium temperature

	Туре	Article no.	For valve type	G	Rp
				[inch]	[inch]
\$ \\ \frac{1}{8} \\ \frac{8}{8} \\ \frac{1}{8} \\ \	ALS202	BPZ:ALS202	VVG44.15	G 1	26.8
Q 4363M02a	ALS252	BPZ:ALS252	VVG44.20	G 1¼	33.7
	-	-	VVG44.25	-	-
(7)	-	-	VVG44.32	-	-
	-	-	VVG44.40	-	-

#### **Filter**

	Туре	DN	b	С	G	L	Н	K <sub>vs</sub>	Weight
			mm	mm	Inch 1)	mm	mm		kg
L H 50000	ALX15	15	12	38	G ½	54	27	3.5	0.178
	ALX20	20	15	43	G ¾	67	34	5.8	0.290
	ALX25	25	16	53	G 1	79	41	9.1	0.410
	ALX32	31	17	64	G 1¼	98	51	19	0.680
	ALX40	40	18	70	G 1½	106	57	24	0.874
	ALX50	50	20	85	G 2	122	69	36	1.428

<sup>1)</sup> ISO 228-1

#### Replacement parts

Туре	Item no.	Designation	Quantity
74 676 0273 0	74 676 0273 0	Rotary knob for small-stroke valves	10

#### Revision numbers

Туре	Valid from rev. no.	Туре	Valid from rev. no.		
VVG44 2-port		VXG44 3-port			
VVG44.15-0.25	A	VXG44.15-0.25	A		
VVG44.15-0.4	A	VXG44.15-0.4	A		
VVG44.15-0.63	A	VXG44.15-0.63	A		
VVG44.15-1	A	VXG44.15-1	A		
VVG44.15-1.6	A	VXG44.15-1.6	A		
VVG44.15-2.5	A	VXG44.15-2.5	A		
VVG44.15-4	A	VXG44.15-4	A		
VVG44.20-6.3	A	VXG44.20-6.3	A		
VVG44.25-10	A	VXG44.25-10	A		
VVG44.32-16	A	VXG44.32-16	A		
VVG44.40-25	A	VXG44.40-25	A		

Issued by
Siemens Switzerland Ltd
Smart Infrastructure
Global Headquarters
Theilerstrasse 1a
6300 Zug
Switzerland
Tel. +41 58-724 24 24
www.siemens.com/buildingtechnologies

© Siemens Switzerland Ltd, 2016 Technical specifications and availability subject to change without notice.

Document ID A6V10960349\_en--\_d
Edition 2023-01-26