

## Pressure Independent Control Series 2-Way Flanged Valves and Electromotoric Valve Actuators




### Description

The 2-1/2-inch and 3-inch Pressure Independent Control Valves have a 20 mm stroke, and work with the SAX and SQV Series Electromotoric Actuators. The 4- and 5-inch valves have a 40mm stroke, and the 6- and 8-inch valves have a 43 mm stroke and work with the SAV and SQV Series Electromotoric Actuators. The actuators require a 24 Vac/dc operating voltage and accept floating, 0 to 10 Vdc, or 4 to 20 mA control signals.

Typical applications include control of hot or chilled water or water-glycol solutions up to 50% in closed loop systems.

### Product Numbers

Use the product numbers in the tables to order the valve and the actuator assembled together. The product number consists of a 3-digit prefix code, a hyphen, and a 5-digit code. The prefix specifies an actuator. The 5-digit code specifies the valve body. See Table 2.



**Table 1. Reference: Valve Body Maximum Flow Range.**

Valve Body	Line Size Inch (mm)	Maximum GPM Flow Range
599-07330	2-1/2 (65)	21 to 132
599-07335		
599-07331	3 (80)	31 to 195
599-07336		
599-07332	4 (100)	64 to 370
599-07337		
599-07333	5 (125)	78 to 525
599-07338		
599-07334	6 (150)	106 to 740
599-07339		
599-07340	8 (200)	418 to 925
599-07345		

### Features

The Pressure Independent Control Valves include a pressure regulator, a flow limiter, and a control valve in a single device.

SAX, SAV, and SQV Actuators have a direct-coupled installation, manual override and visual position indication.

### Technical Data

#### Valve Specifications

Body material:	Cast iron
Stem:	Stainless steel
Line size:	2-1/2-inch (65 mm) to 8-inch (200 mm)
Action:	2-way
Valve body rating:	ANSI 125 or ANSI 250
Close-off:	116 psi (800 kPa) Δp
Leakage rate:	< ANSI Class IV (0.01%)
Media temperature range:	34°F to 250°F (1°C to 121°C)
Flow characteristic:	Linear
Connection:	ANSI flanged

#### Actuator Specifications

Operating voltage:	SAX, SAV, SQV	24 Vac/dc
Frequency:		50/60 Hz
Power consumption (normal operation):	SAX61.03U/SAV61.00U	8 VA (3.75W)/9.5 VA (4.5W)
	SQV	20 VA/7.5W
Control Signal:	SAX61.03U/SAV61.00U	0 to 10 Vdc, 4 to 20 mA
	SQV	Selectable (Floating, 0 to 10 Vdc, 4 to 20 mA)
Run time:	SAX	30 seconds
	SAV	120 seconds
	SQV	40 to 240 seconds (adjustable)
Force:	SAX	180 lb (800 N)
	SAV	360 lb (1600 N)
	SQV	250 lb (1100 N)
Weight:	SAX	4.1 lbs (1.85 kg)
	SAV	4.23 lbs (1.92 kg)
	SQV	14 lbs (6.2 kg)

#### Additional References:




Technical Instructions	
PICV Valves	155-522
SAX Actuators	155-506
SAV Actuators	155-547
SQV Actuators	155-521
Agency Certifications (SAX, SAV, SQV):	
UL	UL 873
cUL	Canadian Standard C22.2 No. 24

## Typical Specifications

Flow shall be varied by actuator position. At any given position, flow through the valve shall not vary more than  $\pm 5\%$  due to system pressure fluctuations across the valve in the selected operating range.

Valves shall be pressure independent between a differential pressure of  $\leq 5$  to 90 psi for low-flow valves and new 599-073XX valves, or  $\leq 10$  to 90 psi for high-flow valves. Length of stroke shall be consistent and independent of flow setting.

**Table 2. 2-1/2-Inch to 6-Inch 2-Way Valve and Actuator Assemblies.**

Valve Body	ANSI Class	Line Size, Inch (mm)	Maximum Flow	Non-Spring Return		Spring Return	
				SAX61.03U 0 to 10V	SAV61.00U 0 to 10V	SQV91P30U Normally Open	SQV91P40U Normally Closed
							
				Actuator Prefix Code			
				371	378	238	239
599-07330	125	2.5	132	371-07330	-	238-07330	239-07330
599-07335	250	(65)		371-07335	-	238-07335	239-07335
599-07331	125	3	195	371-07331	-	238-07331	239-07331
599-07336	250	(80)		371-07336	-	238-07336	239-07336
599-07332	125	4	370	-	378-07332	238-07332	239-07332
599-07337	250	(100)		-	378-07337	238-07337	239-07337
599-07333	125	5	525	-	378-07333	238-07333	239-07333
599-07338	250	(125)		-	378-07338	238-07338	239-07338
599-07334	125	6	740	-	378-07334	238-07334	239-07334
599-07339	250	(150)		-	378-07339	238-07339	239-07339
599-07340	125	8	925	-	378-07340	238-07340	239-07340
599-07345		(200)	1233	-	378-07345	238-07345	239-07345

Information in this publication is based on current specifications. The company reserves the right to make changes in specifications and models as design improvements are introduced. Products or company names mentioned herein may be the trademarks of their respective owners. © 2022-2026 Siemens Industry, Inc.