

### Desigo™ Room Automation

# Compact actuating room automation stations, BACnet MS/TP, AC 24 V (Actuating DXR)

DXR1.M09PDZ-112, DXR1.M09PLZ-112, DXR1.M09PDZ-113



Combination of room automation station and actuator for buildings with increasing demand on functionality and flexibility in Room Automation, VAV and FPB applications.

- Compact, configurable room automation station in combination with actuator for HVAC
- QMX1.M34H and QMA1.N30H room unit
- BACnet MS/TP communications (BTL certified)
- USB interface
- Operating voltage AC 24 V
- Built-in 5 or 10 Nm actuator
- Internal 0...500 Pa differential pressure sensor
- Plug-in terminal blocks





#### Configurable

The DXR1.. automation stations provide the infrastructure for systems and applicationspecific functions which can be configured.

#### **Compact series**

The compact build allows direct mounting on the damper shaft. It is designed for VAV and FPB.

#### Plug-in terminal blocks

Plug-in terminal blocks for easy exchange of room automation stations.

#### Integrated actuator

The actuator gear base is integrated into the housing of the actuating DXR. It supports dampers with up to 5 or 10 Nm torque.

#### Use

Desigo Room Automation offers the highest level of flexibility for energy-optimized solutions while satisfying requirements for temperature control, ventilation and comfort using standard tools and established workflows.

#### Pre-installed application types

- Variable (VAV), Fan Powered Box (FPB) and constant air volume flow
  - with staged and modulating electric heating
  - with modulating hot water/chilled water with room or supply temperature control

#### **Application options**

- Separate temperature and air volume flow setpoints for all 4 operating modes
- Separate minimum and maximum cooling and heating flow setpoints
- Single-stage, multiple-stage or variable fan control (FPB/DXR1.M09PDZ-113)
- Chilled water and hot water valve
- Extract air volume flow control

#### **Functions**

The selected application and its parameters as well as input and output configuration determine the automation station's functionality.

A detailed description of functionality is available in the ABT (Automation Building Tool) online help.

#### Communication

- BACnet MS/TP
- USB connection for service, commissioning and firmware download

#### LED indication

LED	Color		Function
Run	Run Green	Steady ON	Device is ready for operation
		Steady OFF	Device is not powered


2

LED	Color		Function
		Regular flashing	Start-up or the program is stopped
		Steady OFF	ок
	Red	Steady ON	Program error Hardware fault
		Rapid flashing	Wrong or corrupt software No application loaded
		Blinking per wink command	Physical device identification
		5 Hz	21 s 922:62 5 Hz

## Service button (SVC)

Physical identification on the network.

## Technical / mechanical design



1	Service button (SVC) for sending device identification	2	2 UIs (universal input), 1 AO (analog output)
3	Power supply	4	RJ45 interface for room unit
5	4 DOs (digital Triac output)	6	Status information LED (bi-color)
7	BACnet MS/TP		

#### Housing

The housing consists essentially of flame retardant, non-brominated plastic.

#### Type summary

Product No.	Stock No.	Inputs	Outputs	Description	Quantity
DXR1.M09PDZ- 112 (5 Nm)	S55499-D462	2 universal inputs	4 digital outputs, 1 analog output	VAV application	Single package / multiple package (10)
DXR1.M09PLZ-112 (10 Nm)	S55499-D741	2 universal inputs	4 digital outputs, 1 analog output	VAV application	Single package / multiple package (10)
DXR1.M09PDZ- 113 (5 Nm)	S55499-D463	2 universal inputs	4 digital outputs, 1 analog output	FPB application	Single package / multiple package (10)

#### Ordering

When ordering, indicate product number, stock number and description.

#### **Equipment combinations**

Product No.	Stock No.	Designation	Datasheet*
QMA1.N30H	S55499-D464	Room temperature sensor for DXR1 (without LCD)	A6V11393922
QMX1.M34H	S55499-D465	Room unit for DXR1 (with LCD)	A6V11393927

<sup>\*</sup> The documents can be downloaded from <a href="http://siemens.com/bt/download">http://siemens.com/bt/download</a> by specifying the Datasheet number as shown in the above table.

#### Product documentation

Topic	Title	Document ID:
Installation, cable length, topology	Desigo Room Automation installation guide	CM111043
Engineering and commissioning	ABT online help	N/A
Installation instruction	Mounting instructions	A6V11393918
Commissioning	Quick guide	A6V11526405
Product environmental declaration		A6V11805930
EU declarations (CE)		A6V11791489

Documents such as environmental declarations, CE declarations, etc., can be downloaded at the following Internet address:

http://siemens.com/bt/download

Siemens

#### Security

## **A** CAUTION



#### National safety regulations

Failure to comply with national safety regulations may result in personal injury and property damage.

- Observe national provisions and comply with the appropriate safety regulations.
- Use only properly trained technicians for mounting, commissioning and servicing.

#### **Engineering**

#### Identification

Each device has a unique serial number to ensure efficient commissioning. It is provided on the adhesive barcode reader. The serial number can be read directly into the engineering tool using a barcode reader.


#### Wiring

Wiring must be sufficiently insulated to the available rated voltage. Sizing and fusing of the wiring depend on the connected load.

#### Mounting

Smart Infrastructure

The automation station is mounted directly on a damper shaft.



See the mounting instructions (document ID: A6V11393918) for detailed information.

#### Differential pressure sensor

- Avoid bends and pressure when attaching the tube.
- Connect the "+" connection on the side with the higher pressure and the "-" connection on the side with the lower pressure.
- Connection tubes (interior diameter) of 4 mm.
   Air tube connection kit DXA.T50 for connection of tubes with 6.5 mm (interior diameter).
- The maximum tube length is 2 m.

Applies to devices with supply output (AC 24 V or mains voltage) such as Triac output or output to supply a field device.

#### **A** WARNING



No internal line protection for supply lines to external consumers

Risk of fire and injury due to short-circuits

Adapt the line diameters as per local regulations to the rated value of the installed fuse.

#### **Maintenance**

The automation station is maintenance-free.

#### **Disposal**



The device is considered an electronic device for disposal in accordance with European Directive and may not be disposed of as domestic waste.

- Use only designated channels for disposing the devices.
- Comply with all local and currently applicable laws and regulations.

#### Warranty

Technical data on specific applications are valid only together with Siemens products listed under "Equipment combinations". Siemens rejects any and all warranties in the event that third-party products are used.

## Power data

Power supply		
Operating voltage (SELV/PELV) AC 24 V +/-20 %		
Frequency	50 or 60 Hz	
Power consumption	5.5 VA max.: DXR1.M09PDZ-112, DXR1.M09PDZ-113	
	6 VA max.: DXR1.M09PLZ-112	

Transformer requirements and recommended voltages	
Туре	Class 2, AC 24 V, 50 / 60 Hz, SELV, PELV

## **Functional data**

Functional data		
Nominal torque	5 Nm / 10 Nm	
Nominal rotary angle	90 °	
Maximum rotary angle	95°±2°	
Runtime for 90 ° rotary angle	150 s	
Shaft size	816 mm, round 810 mm, round (with centering insert) 612.8 mm square	
Minimum shaft length	20 mm	

## Universal inputs

Analog inputs: DC 010 V	
Operating range 010 V	
Resolution	10 mV

Analog inputs: sensors			
Туре	Measuring range	Accuracy	Resolution
LG / DIN-Ni 1000	050 °C	+/- 0.5 K at 25 °C	0.1 K at 25 °C
Pt1K, 375 / 385			
NTC10K / NTC100K			

Digital inputs	
0/1 digital signal (binary)	For potential-free contacts
Sampling voltage/current	DC 15 V, 7 mA

Digital inputs	
Contact resistance	Max. 200 $\Omega$ (closed) Min. 50 k $\Omega$ (open)
Delay	10 ms
Pulse frequency	Max. 20 Hz

## Outputs

Analog output	
Control range	010 V
Resolution	50 mV
Output current	Max. 1 mA

Triac outputs		
Number of channels	4	
Туре	Requires AC 24 V source to allow switching: switching to phase (AC 24 V) or neutral ()	
Current rating	0.5 A max. per channel	
Voltage rating	AC 24 V +/-20 %	
Max. load	12 VA per channel	
Protection	Short-circuit proof	

#### Pressure sensor

Pressure sensor		
Measurement range	0500 Pa	
Sample rate	≤ 500 ms	
Overload range	0100 kPa	
Measuring range accuracy Zero point accuracy Resolution	3 % 0.2 Pa 16 Bit	

Interfaces	
MS/TP	Terminal: 5.08 mm, 3 pin
	Cable: RS485 shielded STP twisted pair, 18 AWG
	Maximum network length :1000 m
	Point to point length: 500 m
	Termination resistor: 120 Ω
	Bitrates: max. 115.2 kbps
	Galvanic isolation: Yes
	Short-circuit proof Protection against faulty wiring at max. AC 24 V
USB (2.0)	Type Micro B
Interface for room unit (QMA1.N30H and QMX1.M34H)	RJ45 (shield CAT 5-E) Max. wiring length: 30 m

Default network settings	
Mac address	Auto
Baud rate	76800
Network number	1

Wiring connections	
Wiring lengths for signals	MS/TP: max. 1000 m
	Signal lines: max. 80 m
	For analog inputs: max. 30 m

## Conformity

Ambient conditions and protection classification	
Classification per IEC/EN 60730	
Function of automatic control devices	Type 1
Pollution degree	2
Overvoltage category	III
Design type	Device suited for use with equipment of safety classes I and II

Ambient conditions and protection classification		
Degree of protection of housing to IEC EN 60529  Room automation station	IP20	
Climatic ambient conditions	11 20	
Transport (packaged for transport) as per	Class 2K3	
IEC EN 60721-3-2	Temperature -2570 °C	
	Air humidity 595 % (non-condensing)	
Operation as per IEC/EN 60721-3-3	Class 3K5	
	Temperature -550 °C	
	Air humidity 595 % (non-condensing)	
Mechanical ambient conditions		
Transport as per IEC/EN 60721-3-2	Class 2M2	
Operation as per IEC/EN 60721-3-3	Class 3M2	

Standards, directives and approvals		
Product standard	IEC/EN 60730-1 Automatic electronic controls for household and similar use	
EU conformity (CE)	A6V11791489	
RCM conformity	A6V11791498	
EAC conformity	Eurasian conformity	
UL Approbation Federal Communications Commission	UL as per UL916, http://ul.com/database cUL as per CSA – C22.2 No. 205 FCC CFR 47 Part 15 Class B	
ICES003	CAN ICES-3 (B)/NMB-3(B)	
Environmental compatibility	The product environmental declaration (A6V11805930*) contains data on environmentally compatible product design and assessments (RoHS compliance, materials composition, packaging, environmental benefit, disposal).	

<sup>\*</sup> The documents can be downloaded from <a href="http://siemens.com/bt/download">http://siemens.com/bt/download</a>.

#### **FCC** regulations

## Modification of this device to receive cellular radio telephone service signals is prohibited under FCC rules and federal law.

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

Reorient or relocate the receiving antenna.

Increase the separation between the equipment and receiver.

Connect the equipment into an outlet on a circuit different from that to which the receiver is connected. Consult the dealer or an experienced radio/TV technician for help.

Siemens

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

#### **Statement**

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.


#### General

General information	
Color	Light gray
Dimensions	L × W × H = 137 × 143 × 82 mm
Weight	Net weight: 620.2 g Gross weight: 845.1 g

#### Diagrams

#### **Connection terminals**

#### DXR1.M09PDZ-112, DXR1.M09PLZ-112 and DXR1.M09PDZ-113




Pin	Description	Terminal
1113 MS/TP	MS/TP connection	<b>↓</b> , -, +
USB	USB interface	•<
8182 power	Power supply AC 24 V	V~

Pin	Description	Terminal
24 V~	System neutral (must always be grounded at the transformer)	上
6466 inputs	Universal inputs	X1, X2
62, 63 outputs	DC 010 V output	Y10
5456 Triac outputs	Digital output, switching to phase (AC 24 V) or neutral (⊥)	Y3, Y4
5759 Triac outputs	Digital output, switching to phase (AC 24 V) or neutral (丄)	Y5, Y6
Room unit connection	RJ45 interface	
ΔP differential pressure detector	Connected to the higher pressure	P1+
	Connected to the lower pressure	P1-
Service	Service button	svc
Display	Operation LED	RUN

## Dimensions

#### Dimensions in mm



Issued by
Siemens Switzerland Ltd
Smart Infrastructure
Global Headquarters
Theilerstrasse 1a
CH-6300 Zug
+41 58 724 2424
www.siemens.com/buildingtechnologies

© Siemens 2019 Technical specifications and availability subject to change without notice.

Document ID A6V11393929\_en--\_g
Edition 2023-05-30