SIEMENS



ACVATIX™

Electromotive actuators for SQV..P.. PICVs

For PICVs (pressure independent combi valves) VPF43.., VPF44.. and VPF53..

- SQV91.. Operating voltage AC/DC 24 V, Positioning signal 3-position, DC 0-10 V, DC 4-20 mA
- Position feedback and selection of flow characteristic
- Manual adjuster, position and status indication (LED)
- Selectable positioning times 40-240 seconds
- Fail-safe function (PICV open/closed)
- Selection of acting direction
- Optional functional extension: Auxiliary switch, potentiometer, and AC 230 V module
- Direct mounting on PICVs
- UL Listed

Use

Electromotive actuators to operate Siemens PICVs for type series VPF43.., VPF44.. and VPF53.. with 20/40/43 mm stroke, as control valves for ventilation, air conditioning, district heating and refrigeration plants.

Type summary

			Pos.	Operating	Positioning	Spring	Pos. ti	me ²⁾	Fail-safe
Туре	Stock No.	Stroke	force	voltage	signal	return time	20mm	40mm	function
SQV91P30	S55150-A130	00/40/42	1400 N	AC/DC 24 V	3-position	20	40 sec 60 sec	80 s 120 s	Stem retracts
SQV91P40	S55150-A131	20/40/43 mm	1100 N	AC 230 V ¹⁾	DC 010 V DC 420 mA	30 sec	90 sec 120 sec		Stem extends

¹⁾ AC 230 V requires accessory ASP1.1.

 $^{2)}$ The positioning time can be selected using the DIL switch, see page 7.

Electrical accessories

Туре	Auxiliary switch pair ASC10.42	Potentiometer ASZ7.6/1000	AC 230 V module ASP1.1
Stock number	S55845-Z137	S55845-Z136	S55845-Z138
SQV91P30	Ма	Max. 1	
SQV91P40	Ma	Max. 1	

Spare parts, rev.No spare parts available.numberRevision numbers, see page 14.

Ordering

Example	Туре	Stock number	Designation	Quantity
	SQV91P40	S55150-A131	Actuator	1
	ASZ7.6/1000	S55845-Z136	Potentiometer	1


Delivery

Actuator, PICV, and accessories are individually packed for delivery.

Equipment combination

Valv	e type	DN	PN class	Flow V ₁₀₀ [m ³ /h]	Data sheet
4315205	PICVs				
		50		2,325	
		65		4,435	
		80		5,343	
VPF43	Flange	100	16	12,190	N4315
		125		18,5135	
		150		25,6195	
		200		95280	
		50		2,926,2	
VPF44	Flange	65	16	435,8	A6V11466366
		80		5,547,9	
		50		2,325	
		65		4,435	
		80		5,343	
VPF53	Flange	100	25	12,190	N4316
		125		18,5135	
		150		25,6195	
		200		95280	

Technology/Mechanical design



The actuator can be operated as a 3-position or modulating actuator in two acting directions depending on the type of connection. It is suitable for both PICVs VPF.. with 20 mm stroke as well as for valves with a 40 mm and 43 mm stroke. The stroke is calibrated automatically during initialization.

The actuator includes a position feedback.

The actuator travels to the end position in the event of power loss, see "Fail-safe function", page 5. Up to 45 seconds pass until the actuator is available again following a restart or start after the fail-safe function is triggered.

The positioning time (40 to 240 seconds) and the flow characteristic (lin/log) can be set via the DIL switches.

Auto mode	The manual adjuster is disengaged.				
Manual mode	The manual adjuster allows for manually setting the position. The motor is switched off when the manual adjuster is engaged. The fail-safe function (spring return) is reactivated after the manual adjuster is disengaged, and the actuator travels again to the set position without calibration. The actuator remains in this position without active operating voltage for as long as the manual adjustor is engaged.				
Initialization, automatic coupling, calibration	The actuator independently calibrates itself for each type of connection. Initialization occurs as soon as operating voltage is supplied for the first time and the waiting period ends. The actuator travels to the lower stop of the PICV, thus enabling automatic coupling with the valve stem. It then travels to the upper stop, records and stores it. Recalibration can be manually triggered any time, see "Recalibration", page 5.				
3-position control signal	The PICV can travel to any position by supplying voltage to terminal G1 or G2 as well as $L1^{1}$ or $L2^{1}$.				
	 Voltage on G2, L2: Voltage on G1, L1: No voltage on G1 and G2: or L1 and L2: 	Actuator stem retracts, PICV opens. Actuator stem extends, PICV closes. Actuator stem stays at the applicable position.			
	¹⁾ When using the AC 230 V module ASP1.	1.			
Changeover of acting direction	The acting direction of the stroke direction can be reversed by exchanging connections G1 and G2 or L1 and L2.				
Direct acting	Positioning signal OPEN on G2, L2	2. Positioning signal CLOSED on G1, L1.			
Reverse acting	Positioning signal OPEN on G1, L1	1. Positioning signal CLOSED on G2, L2.			
Notes	 Do not use connection Yu (DC 0-10 V) and Yi (DC 4-20 mA). Positioning times can be selected, see "Positioning times", page 7. Valve characteristic curves "lin" or "log" cannot be selected. Position feedback U is activated after initialization/calibration. 				
	reaching maximum stroke) or by ove	ed in the end positions (valve stop or upon rload (no end switch).			
Positioning signals Yu and Yi DC 0-10 V (Yu) DC4-20 mA (Yi)	The PICV can be driven to any position by connecting a continuous positioning signal Yu or Yi. The acting direction can be reserved (direct/reverse acting) by connecting operating voltage to G1 or G2:				
Direct acting	Operating voltage AC/DC 24 V on G	1 or AC 230 V on L1			
	 Pos. signal to Yu, Yi increasing: Actuator stem retracts, PICV opens. Pos. signal to Yu, Yi decreasing: Actuator stem extends, PICV closes. Pos. signal to Yu, Yi continuous: Actuator stem remains in the respective pos. 				
Reverse acting	 Operating voltage AC/DC 24 V on G2 or AC 230 V on L2 Pos. signal to Yu, Yi increasing: Actuator stem extends, PICV closes. Pos. signal to Yu, Yi decreasing: Actuator stem retracts, PICV opens. Pos. signal to Yu, Yi continuous: Actuator stem remains in the respective pos. 				

Acting direction	Position signal	Operating voltage	Actuator stem	PICV
Direct acting	Yu, Yi increasing	G1 to AC/DC 24 V	Retracts	Opens
Reverse acting		L1 to AC 230 V		
	Yu, Yi increasing	G2 to AC/DC 24 V	Extends	Closes
	_	L2 to AC 230 V		

Notes

- The input with the higher value has priority when a positioning signal is available at both Yu and Yi.
- When using the AC 230 V module ASP1.1, the SQV..P can also be operated with a DC 0...10 V or DC 4...20 mA positioning signal.
- The actuator travels to the applicable end position depending on the selected acting direction if Yu or Yi are interrupted:

Operating voltage to G1 or L1	Actuator stem extends.
Operating voltage to G2 or L2	Actuator stem retracts.

- Positioning times can be selected, see "Positioning times", page 7.
- Valve characteristic curves "lin" or "log" can be selected.
- Position feedback U is activated after initialization/calibration.
- Parallel operation with up to 5 actuators possible, see "Technical data", page 11.

Position feedback U

Position feedback U (DC 0...10 V) is always proportional to stroke H for the actuator. It is also active when using the AC 230 V module ASP1.1.

DIL switch	Flow characteristics	Position feedback U
lin = linear ¹⁾	H, V MOZEEBP Y	
log = equal percentage, n _{gl} = 3 (logarithmic normal)	A H, V	
log = equal percentage, n _{gl} = 3 (exponential normal)	H, V 902EE8P	

¹⁾ Factory setting

Fail-safe function

The actuator travels to the applicable end position (the stem retracts or extends depending on the model) using the preloaded spring if operating voltage to terminal G or 21 is lost or shut down. In this case, the actuator's control function is locked for 45 seconds (both LEDs are green) to reach the end position at any rate. There is no recalibration. The reset positioning speed ensures that no pressure surges occur in the piping.

5/14

End position	SQV91P30 SQV91P40	Actuator stem retracted Actuator stem extended	PICV opened (V = 100%). PICV closed (V = 0%).			
Recalibration	Recalibration can be manually triggered any time.					
	 Operating voltage is supplied. Engage and disengage the manual adjuster twice within 4 seconds. Both LEDs flash green. Recalibration is successful when both LEDs are lit green. Return to normal control function. 					
 Notes Position feedback U is inactive or corresponds to value "0". The shortest possible runtime is initialized. Recalibration is valid only after the entire process is completed. Additional engaging the manual adjuster interrupts the process. 						
Blockade detection	The valve actuator indicates detected blockage by setting the feedback signal to 0 V after ca. 90 seconds. The actuator, however, tries to overcome the blockage during this period. Normal control function is reactivated if the blockage is overcome and position feedback U is once again available.					
Response at the end positions	Blockade detection is always operational. In other words, the actuator demonstrates the following response at end positions H_{100} and H_0 not only during initialization and calibration, but also during normal control operation:					
	 The actuator travels to the end position; the LED is lit in the direction of travel. It detects the end position; both LEDs are lit green. It then briefly travels in the opposite direction; the LED is lit in the direction of travel. It then returns to the end position; LED is lit in the direction of travel It detects the end position; both LEDs are lit green. 					
	exponentially	e is repeated with time intervals 7. The intervals are: 25 seconds 1 min 40 seconds 6 min 40 seconds 26 min 1 h 46 min 40 seconds 7 h 6 min 40 seconds day 4 h 26 min 40 seconds	s between travels increasing			


for the previous interval.

Status and acting direction indication (LED) The status and acting direction indication consists of two green, lit LEDs.

Indication	-	Function
	 LED flashes green LED flashes green 	 Initialization. Manual mode. Delay after operating voltage is supplied, or the fail-safe function is triggered.
48.33Z09	 Steady green 	Actuator stem retracts.
	Steady green	Actuator stem extends.
483211	Steady greenSteady green	End position reached.
4832712 	 LED flashes green 	Blockage or foreign object detected during retraction.
4832713 	 LED flashes green 	Blockage or foreign object detected during extension.
4833Z14	•	No operating voltage

Frost protection thermostat

The actuators can be operated using a frost protection thermostat or temperature detector, see "Connection diagrams", page 12.



- 1 Status and acting direction indication (LED)
- 2 DIL switch
- 3 Connection terminals

DIL switch Positioning times

		Positioning time 1)	
DIL switch	Speed	20 mm	40 mm
ON 1 2 3 4	2 sec/mm	40 sec 2)	80 sec 2)
	3 sec/mm	60 sec	120 sec
ON 1 2 3 4	4,5 sec/mm	90 sec	180 sec
ON 1 2 3 4	6 sec/mm	120 sec	240 sec

¹⁾ Tolerance: ± 1 sec

²⁾ Factory setting

DIL switch Flow characteristics

The flow characteristics can be used only for connections with constant positioning signals DC 0...10 V and DC 4...20 mA.

DIL switch	Flow characteristics	
	lin = linear ¹⁾	
	log = equal percentage, n _{gl} = 3 (logarithmic normal)	A H, V
	log = equal percentage, n _{gl} = 3 (exponential normal)	A H, V

¹⁾ Factory setting

Accessories


Туре	ASC10.42	.42 ASZ7.6/1000	
Stock no.	S55845-Z137	S55845-Z136	S55845-Z138
	Auxiliary switch pair	Potentiometer	AC 230 V module
	4833Z18	4833217	4833Z16
	Switching points can be	01000 Ω	AC 230 V to AC 24 V
	continuously adjusted		converter
	between 0 and 100%		
Installatio	Max. 1		Max. 1
n			

See section "Technical data" (page 11) for more information.

110100				
Engineering	Install electrical connections in accordance with local regulations on electric installations as well as internal or connecting diagrams as of page 10.			
	Observe safety and property a	-	restrictions design	ed to ensure the safety of people
<u>^</u> ▲	 An internal controller controls the actuator for 3-position or DC 420 mA positioning signal connection types, see "Connection diagrams", page 12. For DC 010 V connections (input impedance R_i = 100 kΩ), up to 5 actuators can be controlled in parallel by a controller with a rating of 1 mA. The switching points must be entered on the plant diagram when using the double auxiliary switch ASC10.42. Do not insulate the actuator console and valve stem, as air circulation must be ensured. Non-observance of the above may result in accidents and fires! Do not touch the hot parts without prior protective measures to avoid burns! For permitted temperatures, see "Technical data", page 11. 			
Mounting	Mounting instructions 74 319 0821 0 on mounting PICVs are included in the actuator's packaging. Mounting instructions for accessories are located in the respective packaging.			
	Accessories	_	Mounting instru	ctions
	ASC10.42	S55845-Z137	M4833.1	74 319 0860 0
	ASZ7.6/1000	S55845-Z136	M4833.2	74 319 0861 0

S55845-Z138

Mounting positions



ASP1.1

Commissioning

• Check the wiring and carry out a functional check as part of commissioning.

M4833.3

• Make or check the settings as per the plant diagram for auxiliary switches and potentiometers.

9/14

74 319 0862 0

Maintenance	The actuators are maintenance-free.		
Recommendation	Regularly check functioning (trial) of actuators with safety functions.		
	 When servicing the actuating device: Switch off both pump and operating voltage. Close the main shutoff valve in the piping. Release pressure in the pipes and allow them to cool down completely. Disconnect electrical connections from the terminals as needed. The actuator must be properly installed prior to recommissioning the valve. 		
Recommendation	Trigger stroke calibration after servicing.		
Repair	 There are no spare parts available; the entire actuator must be replaced. Removing the spring on the actuator is prohibited due to the high risk of injury. 		
Disposal			



The device is considered electrical and electronic equipment for disposal in terms of the applicable European Directive and may not be disposed of as domestic garbage.

- Dispose of the device through channels provided for this purpose.
- Comply with all local and currently applicable laws and regulations.

Warranty

Note

The engineering data specified in section "Equipment combination" (page 3) are only guaranteed in connection with the Siemens valves listed.

When using the actuators together with third-party valves, correct functioning must be ensured by the user, and Siemens will assume no responsibility.

Technical data

		SQVP	
Power supply	Operating voltage	AC 24 V ± 20%	
	With ASP1.1 AC 230 V module	DC 24 V \pm 15%	
	Frequency	5060 Hz	
	Fusing ac. DIN 57100 part 430 (supply lines)	6 A10 A slow	
	Power consumption	20 VA / 10 W	
	With ASP1.1 AC 230 V module		
Function data	Positioning times 20 mm	40 1) / 60 / 90 / 180 sec	
	40 mm	80 1) / 120 / 180 / 240 sec	
		The positioning time depends on the DIL switch setting,	
	Desittening frage	"Positioning times ["] (page 7)	
	Positioning force Nominal stroke	1100 N 20 mm / 40 mm / 43 mm	
	Permissible medium temperature (valve fitted)	1120 °C	
Signal inputs	Position signal Terminal G1, G2	3-position	
signal inputo	Voltage	AC 24 V ± 20%	
	Ĵ	DC 24 V ± 15%	
		AC 230 V ± 15%	
	Terminal Yu Voltage	DC 010 V	
	Input impedance Terminal Yi Power	≥100 kΩ DC 420 mA	
	Input impedance	50 Ω	
Fail-safe function 2)	Terminal G / 21 SQV91P30	Loss of operating voltage	
		Actuator stem retracted, PICV fully open (100%).	
	SQV91P40	Loss of operating voltage	
		Actuator stem extended, PICV fully closed (0%).	
	Spring return time 20 mm	15 sec ³⁾	
	40 mm	30 sec ³⁾	
Position feedback	Position feedback U	DC 010 V >2.5 kΩ res.	
	Load impedance Load	Max. 4 mA	
Connecting cable	Wire cross-sectional areas	0.751.5 mm ² , AWG 2016 ⁴⁾	
bonneeting cable	Cable entry	2 entry points M20 x 1.	
		1 entry points M16 x 1.5	
Degree of protection	Housing from vertical to horizontal	IP 66 as per EN 60529	
J	Insulation class	As per EN 60730	
	AC / DC 24 V		
	With ASP1.1 AC 230 V module	11	
Environmental	Operation	IEC 60721-3-3	
conditions	Climatic conditions	Class 3K5	
	Mounting location Temperature General	Indoors (weather-protected) 055 °C	
	Humidity (non-condensing)	<95% r.h.	
	Transport	IEC 60721-3-2	
	Climatic conditions	Class 2K3	
	Temperature	-3070 °C	
	Humidity	<95% r.h.	
	Storage	IEC 60721-3-1	
	Climatic conditions Temperature	Class 1K3 -3065 °C	
	Humidity	595% r.h.	
	Max. media temperature when mounted on	130 °C	
	PICV		
Norms and directives	Electromagnetic compatibility (Application)	For residential, commercial and industrial environments	
	Product standard	EN60730-x	
		CE1T4833xx01 ⁵⁾	
	EU Conformity (CE)		
	RCM Conformity	CE1T4833xx02 ⁵⁾	
	UL Listed	UL 873	
		23BA, 23FR, E75924	
		Identical to the authorized Listee's model numbers -	
		AVF234SF232U & AVF234SF132U	
Environmental		3en ⁵⁾ contains data on environmentally compatible product	
compatibility	design and assessments (RoHS compliance,		
. ,	materials composition, packaging, environmental	hanafit	

	SQVP See "Dimensions" (page 14)		
Dimensions			
Accessories	Potentiometer ASZ7.6/1000 01000 Ω ± 20% Voltage AC / DC 24 V Load < 1 W Double auxiliary switch ASC10.42 Switching capacity AC/DC 12AC 230 V, 6 A resistive, 2 A inductive		
	AC 230 V module ASP1.1 Voltage AC 230 V ± 5% Power consumption 22 VA		

¹⁾ Factory setting

²⁾ Control function is locked for 45 seconds.


³⁾ At +23 °C ambient temperature and 1100 N nominal load

⁴⁾ AWG = American wire gauge.

⁵⁾ The documents can be downloaded from <u>http://siemens.com/bt/download</u>


Connection diagrams

Connection diagrams AC / DC 24 V



N1 actuator

F1 frost protection thermostat




Y1 actuator

N1 controller

F1 frost protection thermostat

Connection terminals



¹⁾ Connect either G1 or G; or L1 or L2. Refer to the description at "Positioning signals Yu and Yi", page 4 for additional details.

3-position

AC / DC 24 V

_ Fail-safe function (system potential)

- _ System neutral
- G2 AC/DC 24 V, acting direction: Actuator stem retracts, PICV fully open (100%) ¹⁾
- G1 AC/DC 24 V, acting direction: Actuator stem extends, PICV fully closed (0%) ¹⁾
- Yu Positioning signal DC 0...10 V (not used for the 3-position operation)
 - Positioning signal DC 4...20 mA (not used for 3-position operation)

Position feedback DC 0...10 V

With AC 230 V module ASP1.1

AC 230 V

 L1
 AC 230 V, acting direction: Actuator stem extends, PICV fully closed (0%) ¹)

 L2
 AC 230 V, acting direction, Actuator stem retracts, PICV fully open (100%) ¹)

 N
 Neutral

 21
 Fail-safe function (phase)



G

G0

Yi


U

Position feedback DC 0...10 V

Positioning signal DC 4...20 mA (not used for the 3-position operation)

Yu Positioning signal DC 0...10 V (not used for 3-position operation)

¹⁾ Refer to the description at "3-position control signal", page 4 for additional details.



> 100 mm	Minimum mounting distance to wall or ceiling, for mounting,
>200 mm	connection, operation, maintenance etc.

Revision numbers

Туре	Revision number	Туре	Revision number
SQV91P30	A	SQV91P40	A

Issued by Siemens Switzerland Ltd Smart Infrastructure Global Headquarters Theilerstrasse 1a 6300 Zug Switzerland Tel. +41 58-724 24 24 www.siemens.com/buildingtechnologies

© Siemens Switzerland Ltd, 2011 Technical specifications and availability subject to change without notice.

14 / 14