SIEMENS



Room thermostat

RAA21...

Adjustable for heating only or cooling only

- 2-position control
- Switching voltage AC 24...250 V

Use

The RAA21.. room thermostat is used in heating only or cooling only systems to maintain the selected room temperature.

Typical use:

- Residential buildings
- Light industrial buildings

In conjunction with


- zone valves or thermal valves
- gas or oil burners
- fans
- pumps

Functions

The RAA21.. room thermostat has separate outputs for heating only and cooling only. If the room temperature falls below the selected setpoint, the heating contact will close. If the room temperature exceeds the selected setpoint, the cooling contact will close.

Smart Infrastructure

Function diagrams



Type summary

Functionality	Product no. (ASN)
Room thermostat for heating or cooling mode	RAA21
Switching voltage AC 24250 V	

Equipment combinations

Description	Product no. (ASN)	Data sheet*)
Motoric on / off actuator	SFA21	4863
Thermal actuator (for radiator valves)	STA21	4893
Thermal actuator (for small valves 2.5 mm)	STP21	4878

Accessories

Description	Product no. (ASN)
Adapter plate 120 x 120 mm for 4 x 4" conduit boxes	ARG70
Adapter plate 96 x 120 mm for 2 x 4" conduit boxes	ARG70.1
Adapter plate for surface wiring 112 x 130 mm	ARG70.2

Technical design

Key features of the RAA21.. room thermostat:

- 2-position control
- · Gas-filled diaphragm

Adjustments


The required temperature setpoint is selected with the setting knob on the front of the thermostat.

The setpoint setting range can be mechanically limited by means of setpoint limiters under the unit cover.

Mounting, installation and commissioning

The thermostat should be located where the room temperature can be acquired as accurately as possible, without getting adversely affected by direct solar radiation or other heat or refrigeration sources.

Mounting height is about 1.5 m above the floor.



The thermostat can be fitted to most commercially available recessed conduit boxes or directly on the wall.

AC 24...250 V

Only authorized personnel may open the unit to perform service. The unit must be isolated from the mains supply before opening. When installing the unit, fix the base plate first, then hook on the thermostat body and make the electrical connections. Then, fit the cover and secure it (also refer to separate mounting instructions). The thermostat must be mounted on a flat wall.

The local electrical regulations must be complied with.

If there are thermostatic radiator valves in the reference room, set them to their fully open position.

Warning!

No internal line protection for supply lines to external consumers (Y1, Y2) Risk of fire and injury due to short-circuits!

• Adapt the line diameters as per local regulations to the rated value of the installed overcurrent protection device.

Maintenance Mechanical design

The room thermostat is maintenance-free. The diaphragm is filled with environment-friendly gas. The housing is made of plastic.

Ordering

Type (ASN)	Part number (SSN)	Description
RAA21	S55770-T220	Room thermostat RAA21

Disposal



The devices are considered electronics devices for disposal in term of European Directive 2012/19/EU and may not be disposed of as domestic waste.


- Dispose of the device via the channels provided for this purpose
- Comply with all local and currently applicable laws and regulations.

Technical data

Power	Switching capacity Voltage Current Frequency	AC 24250 V 0.26(2.5) A 50 or 60 Hz	
A	No internal fuse External preliminary protection with max. C 10 A circuit breaker in the supply line required unc circumstances		
	Screw terminals for	2 x 1.5 mm ² (min. 0.5 mm ²)	
Operational data	Switching differential SD	≤1 K	
	Setpoint setting range	830 °C	
Environmental conditions	Operation Climatic conditions Temperature Humidity Pollution degree	To IEC 60721-3-3 Class 3K5 050 °C <95% r.h. Normal, to EN 60730-1	
	Transport / storage Climatic conditions Temperature Humidity Mechanical conditions	To IEC 60721-3-2 Class 2K3 / 1K3 -2050 °C <95% r.h. Class 2M2	
Industry standards	EU conformity (CE)	8000064801*)	
	UK conformity (UKCA)	A5W00209372A*)	
	RCM conformity	CE1T3561en_C1*)	
	Safety standard Degree of protection of housing	II to EN 60730-1 IP30 to EN 60529	
Environmental compatibility	The product environmental declaration CE1E3561 ⁵ contains data on environmentally compatible product design and assessments (RoHS compliance, materials composition, packaging, environmental benefit, disposal).		
Mechanical design	Weight	0.14 kg (RAA21)	
	Color	White, NCS S 0502-G (RAL 9003)	
	^{*)} The documents can be downloaded from <u>http://siemens.com/bt/download</u> .		


Siemens Smart Infrastructure

Connection diagrams



- Zone valve or thermal valve for heating Zone valve or thermal
- valve for cooling Switching voltage AC 24...250 V
- Room thermostat
- 1 Control output "Heat-
- ing", AC 24...250 V
 - Control output "Cool-
 - ing", AC 24...250 V
 - Neutral conductor Thermostat element
 - (gas-filled diaphragm)

Dimensions



Remarks

Heating:

Because of the unavoidable self heating effects of the electrical current, any loads of more than 3 Amperes connected to the unit can influence the control behavior and temperature accuracy in a negative way.

Cooling:

Because of the unavoidable self heating effects of the electrical current, any loads of more than 1 Amperes connected to the unit can influence the control behavior and temperature accuracy in a negative way.

Smart Infrastructure

© 2011 - 2023 Siemens Switzerland Ltd