SIEMENS



Condensation monitor

QXA2100 QXA2101

Monitor to prevent damage caused by condensation on chilled ceilings and HVAC plants with AC/DC 24 V power.


Application

- Monitors condensation build up in buildings with chilled ceilings or ventilation, air conditioning, and heating plants
- · Prevents condensation on chilled ceilings
- Prevents condensation at critical points in HVAC plants or buildings (ducts, fans, etc.)
- Prevents condensation on surfaces
- Use as a condensation switch

With the sensing element, the condensation monitor records relative humidity close to the dew point (=100 % r. h.). The resistance of the sensing element raises sharply between 90...100 % r. h. The electronics switch the relay prior to reaching the dew point. For example, switching the relay (2-point output) has the following effect on chilled ceiling applications:

- The cool output is switched off through valve position or controller until the condensation signal disappears.
- Water flow temperature is increased immediately to a selectable value (e.g. 1 to 2 2. K) and then slowly lowered after the signal disappears.

The specific control function is required on the controller for this application.



Key

The diagram shows the relay status when power is on. When power is off the relay contact Q11-Q12 is closed.

Note


The detector does not withstand continuous condensation.

Technical design

The device is planned for AC/DC 24 V power with potential free AC/DC 1...30 V changeover contact or with extension module AQX2000 for AC 230 V power with potential free AC/DC 12...250 V changeover contact.

QXA2100

Housing with snap-on cover made of pure white, flame retardant thermoplastics with spring-loaded humidity sensing element, holding relay with changeover contact, connection terminals, and Pg 11 cable entry glands made of plastic.




Key


- Sensing element
- 2 Fixing screw with strap-on band
- 3 Terminal block
- 4 Nose of snap-on facility
- Slot for lifting the cover with the help of a screwdriver
- Connection label

QXA2101

The same as QXA2100, but with remote sensor head (fixed cable connection of 1 m) rather than a directly integrated sensor.

View: Sensor head on the mounting side View: Sensor head front side





- 1 Sensing element
- 2 Tensioning strap
- 3 Connector cable 1 m to base housing

AQX2000

The AQX2000 extension module consists of base, top section, and printed circuit board with lateral connection terminals.




Note

The AQX2000 extension module is not supplied anymore.

RXZ40.1

The RXZ40.1 terminal cover is available as an option for the AQX2000 extension module. It provides protection against electric shock and keeps terminals free from dust and dirt.

When fitting the terminal cover, ensure that it engages correctly.



Removal of terminal cover

Type summary

Туре	Order number	Designation
QXA2100	S55770-T375	Condensation monitor.
QXA2101	S55770-T376	Condensation monitor with offset sensor

Scope of delivery

- a QXA2100 condensation detector or
- a QXA2101 condensation detector with offset sensor.
- a tensioning strap for pipe diameters of 10...100 mm.
- thermal conductive paste.
- · mounting instructions.

Accessories

Туре	Order number	Designation
AQX2000	BPZ:AQX2000	Extension module *)
RXZ40.1	BPZ:RXZ40.1	Terminal cover

^{*)} Not supplied anymore

Equipment combinations

All devices that

- can work with AC/DC 24 V power and the condensation signal from the potential free AC/DC 1...30 V relay changeover contact
- with the help of the AQX2000 extension module, with AC 230 V power, it can work
 the condensation signal from potential free AC/DC 12...250 V relay changeover contact.

Notes

Engineering

The AQX2000*) extension module is operated with AC 230 V power. It provides AC 24 V power for the condensation detector and the condensation signal on the potential free AC/DC 12...250 V relay changeover contact.

*) not available any more

Mounting

Condensation detector QXA2100/QXA2101

- Pipe mounting with tensioning strap (pipe diameter 10...100 mm)
- · Surface-mounting on walls or ceilings with 4 screws

The condensation monitor performs its function only if the humidity sensing element assumes the same temperature as the surface to be protected against condensation. Please note:

- Apply a thin layer of thermal conductive paste on the mounting surface
- Mount at the coldest spot of the chilled ceiling (plant)
- Mount on the water inlet pipe on water-cooled chilled ceilings

Note

Protect the sensing element against aggressive chemicals and dirt, since this can adversely affect the proper operation of the monitor and significantly shorten its life.

The condensation detector is supplied with mounting instructions.

Mounting AQX2000 extension module AC 230 V

- Top hat rails EN 60 715-TH 35-7.5
- Wall mounted (with the help of screws)

Maximum cable length to condensation detector: 20 m

Installation ACCaution!

Electrical voltage

Electric shock


- Work on electrical installations may only be carried out by qualified electricians or by instructed persons working under the guidance and supervision of a qualified electrician, in accordance with the electrical regulations.
- Terminal cover RXZ40.1 must be used when using the AQX2000 extension module outside a closed panel.



Electrical wiring can loosen from the terminals

Fire hazard or risk of injury from electrical shock or short circuiting

 Strain relief required on AC 230 V terminals. Fix wiring with cable bindings (see image below) to the tabs in the housing base.



Commissioning

A functional test can be conducted if needed, by exhaling slowly onto the sensing element several times to simulate condensation.

Note

Do not expose the sensing element to tap water as this can cause electrolytic corrosion.

Power lines AC 230 V Local regulations regulate sizing and fusing of power lines. Power lines must be fused in the extension module AQX2000 with strain relief (see Engineering).

Disposal



This symbol or any other national label indicate that the product, its packaging, and, where applicable, any batteries may not be disposed of as domestic waste. Delete all personal data and dispose of the item(s) at separate collection and recycling facilities in accordance with local and national legislation.

For additional details, refer to. www.siemens.com/bt/disposal.

QXA2100, QXA2101

Power supply G (G+), G0 (G-)	Operating voltage	SELV/PELV AC/DC 24 V ±20 %
	Frequency	50/60 Hz
	Power consumption	Max. 1 VA
	External fuse	Transformer with secondary current limit of max. 10 A or
		 external secondary current fuse with max. T 10 A non-renewable fuse or max. C 13 A circuit breaker Required under all circumstances
Functional data	Cuitabina point on increase in humidity	· · · · · · · · · · · · · · · · · · ·
Functional data	Switching point on increase in humidity	95 ±4 % r. h.
	Switching differential (fixed)	Approx. 5 % r. h.
	Response time in static air 80 to 99 % r. h.	
	99 to 80 % r. h.	Max. 3 min Max. 3 min
Output Q11, Q12, Q14	Relay output	Potential free changeover contact
Output Q11, Q12, Q14	Current range at AC/DC 24 V	0,0011 (1) A
	Starting current at AC/DC 24 V	≤5 A for ≤20 ms
	Switching capacity	Min. AC/DC 5 V, 1 mA
		Max. AC/DC 24 V, 1 A
	External fuse	External fuse at max. T 4 A non- renewable fuse required
Connections	Mechanical	strap-on band for pipe Ø 10100 mm
	Electrical connections Screw terminals for	1.5 mm ²
	Housing	IP 40 per EN 60 529
Protective data	Protection class	III as per EN 60 730
Environmental conditions	Transport to	IEC/EN 60721-3-2
	Climatic conditions	Class 2K12
	Temperature Humidity	-40+70 °C <95 % r. h.
	Mechanical conditions	Class 2M4
	Operation to	IEC/EN 60721-3-3
	Climatic conditions	Class 3K23
	Temperature (housing with electronics)	−5+50 °C
	Humidity Mechanical conditions	595 % r. h. (noncondensing)
Directives, standards	Product standard Automatic electronic controls for household and sim	Class 3M11
		EN 60730-1
	EU conformity (CE)	See EU declaration of conformity 1)
	RCM conformity	See RCM declaration of conformity 1)
	EAC compliance	Eurasian compliance
Materials and colors	Housing	Thermoplastic, pure white, flame retardant
Dimonsions (woight)	Including packaging OYA 2400	0 126 kg
Dimensions (weight)	Including packagingQXA2100 QXA2101	0.126 kg
	QAAZ IU I	0.126 kg


¹⁾ Documents can be downloaded at https://siemens.com/bt/download.

AQX2000

Power L, N	Operating voltage	AC 230 V ±10 %
	Frequency	50/60 Hz
	Power consumption	Max. 4 VA
	External fuse	External secondary current fuse
	External rado	· ·
		 with max. T 10 A non-renewable fuse or
		max. C 13 A circuit breaker Required under all circumstances
Inputs	Status signal input D, GND	
mpato	Contact voltage	DC 37 V (SELV/PELV))
	Contact current	13 mA
Outputs	Voltage output G, G0	
	Rated voltage range	AC 24 V ±20 % (SELV/PELV)
	Frequency at AC 24 V	50/60 Hz
	durable	max. 1 VA
	Relay output Q11, Q12, Q14	Potential free changeover contact
	,,,	Not suitable for connecting to
		SELV/PELV circuits
		Line fusing requires strain relief
		AC/DC 12250 V
	Rated voltage range	0,016 A
	Rated voltage range Rated current range	Min. AC/DC 12 V, 10 mA
	Switching capacity	Max. AC/DC 250 V, 6 A
	omorning depactify	1500 V
	Insulation against power (L, N)	
	External fuse	External secondary current fuse
		• with max. T 6 A non-renewable fuse
		or
		 max. C 6 A circuit breaker Required under all circumstances
Connections	Electrical connections	
	Screw terminals for	Max. 2 x 1.5 mm ² or 1 x 2.5 mm ²
	Wire length to QXA2100, QXA2101	Max. 20 m
Drotostivo doto	Degree of protection of housing	
Protective data	With terminal cover and wall-mounting without top hat rail	
		IP30 to EN 60 529
	Safety class to EN 60 730	device suited for use with equipment of
		safety classes I and II
Environmental conditions	Operation to	IEC/EN 60721-3-3
	Climatic conditions	Class 3K23
	Temperature (housing with electronics)	−5+50 °C
	Humidity	< 85 % r. h.
	Mechanical conditions	Class 3M11
	Transport to	IEC/EN 60721-3-2
	Climatic conditions	Class 2K12
	Temperature	-40+70 °C
	Humidity	<95 % r. h.
	Mechanical conditions	Class 2M4
Directives, standards	Product standard	_
•	Automatic electronic controls for household and similar us	se
		EN 60730-1
	Housing	ARS + DC
Materials	Housing Terminal cover	ABS + PC
	Terminal cover	ABS + PC
Discouries and the state		0.01
Dimensions (weight)	Including packaging	0.2 kg

Internal diagrams

QXA2100, QXA2101




G (G+) Operating voltage AC 24 V or DC 24 V

G0 (G-) System neutral

Potential free changeover contact

AC/DC 1...30 V n/c Do not use

AQX2000



Operating voltage AC 24 V

G0 System neutral
D, GND Status signal input DC 37 V for potential free changeover contact of the QXA2100,


QXA2101

L, N Q...

Operating voltage AC 230 V Potential free changeover contact


AC/DC 12...250 V

Connection diagram



- Condensation detector QXA2100 / QXA2101
- AQX2000 extension module AC 230 V

QXA2100 44 36,5 Pg 11



Published by:
Siemens Switzerland Ltd.
Smart Infrastructure
Global Headquarters
Theilerstrasse 1a
CH-6300 Zug
Switzerland
Tel. +41 58-724 24 24
www.siemens.com/buildingtechnologies

© Siemens Switzerland Ltd 2015 Delivery and technical specifications subject to change

10/10