SIEMENS

Submittal Sheet

Document No. 154-135 January 20, 2017

OpenAir[™] GLB Series, Enhanced Non-spring Return, 88 Ib-in, Direct Coupled, Electronic Damper Actuators

Product Number	Operating Voltage		Control		Pre-Cabled			Built-in Control Options	
	24 Vac/dc +/-20%	100 to 240 Vac +/-10%	0(2) to 10 Vdc	2-Position/Floating	Standard, 18 AWG, 3 ft (0.9 m)	Plenum, 18 AWG, 3 ft (0.9 m)	Plenum, 18 AWG, 6 ft (1.8 m)	Feedback	Dual Auxiliary Switches
GLB141.1P	•			٠		٠			
GLB141.1Q	•			•			•		
GLB146.1P	•			•		٠			•
GLB341.1U		•		•	•				
GLB346.1U		•		•	•				•
GLB161.1P	•		•			•		•	
GLB161.1Q	•		٠				•	•	
GLB166.1P	•		•			•		•	•

Technical Data

Torque: Runtime for 90°: Frequency: Power consumption: GLB14x GLB34x GLB16x Equipment rating (24 Vac): Noise level: Angle of rotation: Shaft dimensions:

Operating temperature: Storage temperature: Ambient humidity: Enclosure:

Material: Agency listings:

CE

Gear Lubrication: Weight With packaging Country of Origin

88 lb-in (10 l	Nm)						
	s opening and	d closing					
50/60 Hz		•					
VA	Watt						
2.2	1.3						
5.8	1.9						
2.5	1.5						
Class 2 per	JL/CSA						
<28 dBA (ru	nning)						
90° nominal,	90° nominal, 95° maximum						
3/8 to 5/8 in. (8 to 16 mm) dia., 3/4 in. (20 mm) min. length							
-25°F to 130	-25°F to 130°F (-32°C to 55°C)						
-40°F to 158°F (-40°C to 70°C)							
95% rh (non-condensing)							
NEMA 2, IP54 per EN60529 (Not with cable-up mounting orientation)							
Durable plas	tic						
UL listed to UL60730, cUL certified to Canadian Standard C22.2 No. 24-93 Plenum areas per UL 1995 EN60730-1, EN60730-2-14 Silicone-free 1.35 lb (0.61 kg)							
1.91 lb (0.87 kg) USA							

Description

The OpenAir, non-spring return, directcoupled, electronic damper actuators provide 2-position/floating and modulating control of building HVAC dampers.



Features

- Selectable modulating control signal (0 to 10 Vdc or 2 to 10 Vdc).
- 24 Vac/dc compatible.
- New line voltage (34x models) for 100 to 240 Vac twoposition/floating control.
- Integral 1/2-inch conduit connection.
- Manual override.
- Low energy consumption.
- Quiet operation.
- Independently adjustable dual auxiliary switches available.
- UL60730 and cuL listed;
 Certified.

Typical Specifications

Non-spring return damper actuators shall be the directcoupled type that requires no connecting linkages. The nonspring return actuators under 100 lb-in shall be capable of direct-mounting to a shaft up to a 5/8-inch diameter. Actuators shall provide stall protection throughout the full range of rotation. All non-spring return actuators shall be capable of both clockwise and counterclockwise operation. All non-spring return actuators shall hold position in the event of a power failure. All modulating actuators shall return to the 0 position in the event only the control signal is lost. All actuators shall provide a means of manually positioning the output coupling in the absence of power. Dual independently adjustable auxiliary switches must be integral to the actuator. All actuators must provide an easily readable high contrast vellow on black position indicator. All actuators shall be UL60730 and CSA22.2 listed, CE certified, and manufactured under ISO 9002 and ISO 14000 procedures. Actuators shall be designed for a minimum of 100,000 full stroke cycles, 5,000,000 repositions at the actuators rated torque and temperatures. Actuators shall be as manufactured by Siemens Industry, Inc.

Dimensions




Figure 1. GLB Actuator Dimensions in Inches (mm).

Information in this publication is based on current specifications. The company reserves the right to make changes in specifications and models as design improvements are introduced. OpenAir is a trademark of Siemens Schweiz AG. Product or company names mentioned herein may be the trademarks of their respective owners. © 2017 Siemens Industry, Inc.


Siemens Industry, Inc. Building Technologies Division 1000 Deerfield Parkway Buffalo Grove, IL 60089 USA Tel. + 1 847-215-1000

Your feedback is important to us. If you have comments about this document, please send them to <u>sbt_technical.editor.us.sbt@siemens.com</u>


Document No. 154-135 Printed in the USA

Wiring Diagrams

GLB14x, 2-Position/Floating Control, 24 Vac/dc:



GLB34x, 2-Position/Floating Control, 100 to 240 Vac:



GLB16x, 0(2) to 10 Vdc Modulating, 24 Vac/dc:

