

UK Declaration of Conformity

No. A5W00198019A-005

Product identification

Electromotoric damper actuators GLB...

Manufacturer

Siemens Schweiz AG

Address

Theilerstrasse 1a
CH-6300 Zug / Switzerland

This declaration of conformity is issued under the sole responsibility of the manufacturer.

The object of the declaration described above is in conformity with the relevant statutory requirements:

S.I. 2016 No. 1101 Electrical Equipment (Safety) Regulations 2016, and related amendments

S.I. 2016 No. 1091 Electromagnetic Compatibility Regulations 2016, and related amendments

S.I. 2012 No. 3032 Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012, and related amendments

Designated standards used or technical specifications in relation to which conformity is declared:

Reference number including Edition

EN IEC 63000:2018

EN 60730-1:2011

EN 60730-1:2016 + A1:2019 + A2:2022

EN 60730-2-14:1997 + A1:2001 + A11:2005 + A2:2008

EN IEC 60730-2-14:2019 + A2:2021 + A1:2022

Reference number including Edition

EN IEC 63044-3:2018

EN IEC 63044-5-1:2019

EN IEC 63044-5-2:2019

EN IEC 63044-5-3:2019

EN 50491-5-1:2010

EN 50491-5-2:2010

EN 50491-5-3:2010

CH-6300 Zug, 29.11.2023

Signed for and on behalf of:

Siemens Schweiz AG

i.V.

Thomas Nitz

Product Management, Portfolio & Innovation Head

i.V.

Rico Jaeggi

Head of R&D Competence Center Zug

This declaration is an attestation of conformity with the indicated statutory requirements but does not imply any guarantee of quality or durability. The safety instructions of the accompanying product documentation shall be observed.

Siemens Schweiz AG

Smart Infrastructure
Global Headquarters

Theilerstrasse 1a
CH-6300 Zug

UK Declaration of Conformity

No. A5W00198019A-005

Product number	Stock number	MLFB number	Additional information
[ASN]	[SEN, SSN, ASN or ID]	[MLFB]	
GLB111.1E/KN	S55499-D198	-	Not valid for S.I. 2016 NO. 1101
GLB111.1E/MO	S55499-D199	6FU1513-1LBxx-xxxx	Not valid for S.I. 2016 NO. 1101
GLB111.9E/MO	S55499-D206	-	Not valid for S.I. 2016 NO. 1101
GLB131.2E	GLB131.2E	6FU1213-1LBxx-xxxx	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB136.2E	GLB136.2E	6FU1213-6LBxx-xxxx	Not valid for EN63044 (EN50491)
GLB141.1E	S55499-D192	6FU1114-1LBxx-xxxx	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB141.1E/09H	S55499-D357		Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB141.1H	S55499-D443		Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB141.9E	S55499-D204	-	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB142.1E	S55499-D193	6FU1114-2LBxx-xxxx	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB146.1E	S55499-D194	6FU1114-6LBxx-xxxx	Not valid for EN63044 (EN50491)
GLB161.1E	S55499-D270	6FU1116-1LBxx-xxxx	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB161.1E/09H	S55499-D359		Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB161.2E	GLB161.2E	6FU1216-1LBxx-xxxx	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB161.9E	S55499-D277	-	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB161.9E/MO	S55499-D681		Not valid for S.I. 2016 NO. 1101
GLB161.9G/GD	S55499-D451-A546		Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB163.1E	S55499-D271	6FU1116-3LBxx-xxxx	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB163.2E	GLB163.2E	6FU1216-3LBxx-xxxx	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB164.1E	S55499-D272	6FU1116-4LBxx-xxxx	Not valid for EN 50491-x, EN IEC 63044-x
GLB166.1E	S55499-D273	6FU1116-6LBxx-xxxx	Not valid for EN 50491-x, EN IEC 63044-x
GLB181.1E/3	GLB181.1E/3	6FU1318-1LBxx-xxxx	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x

This declaration is an attestation of conformity with the indicated statutory requirements but does not imply any guarantee of quality or durability. The safety instructions of the accompanying product documentation shall be observed.

Siemens Schweiz AG
Smart Infrastructure
Global Headquarters

Theilerstrasse 1a
CH-6300 Zug

UK Declaration of Conformity

No. A5W00198019A-005

Product number	Stock number	MLFB number	Additional information
[ASN]	[SEN, SSN, ASN or ID]	[MLFB]	
GLB181.1E/BA	S55499-D169	6FU1312-1LBxx-xxxx	Not valid for S.I. 2016 NO. 1101
GLB181.1E/KN	S55499-D135	6FU1311-1LBxx-xxxx	Not valid for S.I. 2016 NO. 1101
GLB181.1E/MO	S55499-D167	6FU1313-1LBxx-xxxx	Not valid for S.I. 2016 NO. 1101
GLB181.1EM3	GLB181.1EM3	-	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB331.2E	GLB331.2E	6FU1233-1LBxx-xxxx	Not valid for EN 50491-x, EN IEC 63044-x
GLB336.2E	GLB336.2E	6FU1233-6LBxx-xxxx	Not valid for S.I. 2016 NO. 1101 Not valid for EN 50491-x, EN IEC 63044-x
GLB341.1E	S55499-D195	6FU1134-1LBxx-xxxx	Not valid for EN 50491-x, EN IEC 63044-x
GLB341.9E	S55499-D205	-	Not valid for EN 50491-x, EN IEC 63044-x
GLB346.1E	S55499-D196	6FU1134-6LBxx-xxxx	Not valid for EN 50491-x, EN IEC 63044-x
GLB361.1E	S55499-D197	6FU1136-1LBxx-xxxx	Not valid for EN 50491-x, EN IEC 63044-x

Note	<u>EMC Level:</u> The listed products are suitable for use in residential , commercial , light-industrial and industrial environments.
-------------	--

This declaration is an attestation of conformity with the indicated statutory requirements but does not imply any guarantee of quality or durability. The safety instructions of the accompanying product documentation shall be observed.