



MVL661... Series

Modulating Refrigerant Valves with Magnetic Actuator



Description	Control valves with magnetic actuator, for modulating control of refrigerant circuits.
Features	<ul style="list-style-type: none"> • One valve type for expansion, hot-gas and suction throttle applications. • Hermetically sealed towards outside. • Selectable control signal interface 0/2...10 Vdc or 0/4...20 mA. • High resolution and control accuracy. • Precise positioning control and position feedback signal. • Short positioning time (less than 1 second). • Closed when de-energized. • Robust and maintenance-free. • Five valve sizes with CV (k_{vs}) values from 0.29 to 13.9 (0.25 to 12).
Application	The MVL661...Series refrigerant valves are designed for modulating control of refrigerant circuits including chillers and heat pumps. They can be used in expansion, hot-gas and suction throttle applications as well as with all commonly used safety refrigerants (R22, R134a, R227ea, R404A, R407C, R410A, and so on) and R744 (CO ₂). They are not suitable for flammable refrigerants.
Product Numbers	See <i>Product Summary</i> .

Warning/Caution Notations

WARNING:		Personal injury or loss of life may occur if you do not follow the procedures as specified.
CAUTION:		Equipment damage or loss of data may occur if you do not follow the procedures as specified.

Product Summary

Product Numbers	Line Size Inch (mm)	C _v (k _{vs})	CV (k _{vs}) Reduced ¹⁾	Δp _{max} psi (MPa)	Q ₀ E (kW)	Q ₀ H (kW)	Q ₀ D (kW)	
MVL661.15-0.4	1/2 (15)	0.46 (0.40)		363 (2.5)	47	9.2	1.7	
			0.29 (0.25)		29	5.7	1.0	
MVL661.15-1.0	1/2 (15)	1.2 (1.0)			117	23	4.2	
			0.73 (0.63)		74	14	2.6	
MVL661.20-2.5	3/4 (20)	2.9 (2.5)			293	57	10	
			1.8 (1.6)		187	37	6.6	
MVL661.25-6.3	1 (25)	7.3 (6.3)			737	144	26	
			4.6 (4)		468	92	17	
MVL661.32-12	1-1/4 (32)	13.9 (12)			29 (0.2)	²⁾	²⁾	50
			9.2 (8)			²⁾	²⁾	33

¹⁾ 63% of C_v (k_{vs}), see CV (k_{vs}) Reduction, page 4.

²⁾ MVL661.32-12.0 is only approved for suction throttle applications

K_{vs} Nominal flow rate, in m³/h, of refrigerant through the fully open valve (H₁₀₀) at a differential pressure of 100 kPa (1 bar) to VDI 2173

C_v Nominal flow rate, in gpm, of refrigerant through the fully open valve (H₁₀₀) at a differential pressure of 1 psi.

Q₀ E Refrigeration capacity in expansion applications

Q₀ H Refrigeration capacity in hot-gas bypass applications

Q₀ D Refrigeration capacity in suction throttle applications and Δp = 7 psi (0.5 bar)

Q₀ With R407C at t₀ = 32°F (0°C), t_c = 104°F (40°C).

The pressure drop across the evaporator and condenser is assumed to be 4.35 psi (0.3 bar) each, and 23 psi (1.6 bar) upstream of the evaporator.

The capacities specified are based on superheating by 6K and sub-cooling by 2K.

The refrigeration capacity for various refrigerants and operating conditions can be calculated for the 3 types of applications using Table 4 through Table 9.

For accurate valve sizing, Siemens Industry, Inc. recommends the valve selection program **Refrigeration VASP**.

Ordering

Valve body and magnetic actuator form one integral unit and cannot be separated.

Example:

Product Number	Description	Quantity
MVL661.15-0.4	Refrigerant valve	1

Replacement Parts

If the valve's electronics become faulty, the entire electronics housing must be replaced. Order product number ASR61.

**Technical/
Mechanical Design**

Features and Benefits

- Four selectable control signals.
- DIP switch to reduce the C_V (k_{vs}) value to 63% of the nominal value.
- Potentiometer for adjustment of minimum stroke for suction throttle applications.
- Automatic stroke calibration.
- Forced control input for “Valve closed” or “Valve fully open”.
- LED for indicating the operating state.

Control

The MVL661... Series valve can be driven by Siemens or third-party controllers that deliver a 0 to 10 Vdc/2 to 10 Vdc, 0 to 20 mA/4 to 20 mA control signal.

For optimum control performance, Siemens Industry, Inc. recommends a 4-wire connection between controller and valve.

The valve stroke is proportional to the control signal.




CAUTION:

You must use a four-wire connection with Vdc power supply.

Spring return action

If the positioning signal is interrupted, or in the event of a power failure, the valve's return spring will automatically close control path A → AB.

Operator controls and indicators in the electronics housing



- 1 Connection terminals
- 2 LED for indication of operating state
- 3 Minimal stroke setting potentiometer Rv
- 4 Auto-calibration
- 5 DIP switches for mode control


DIP Switch Configurations

Table 1. DIP Switch Configurations.

Switch	Function	ON/OFF	Description
<p>1</p>	Positioning signal Y	ON	Current (mA)
		OFF	Voltage (V) ¹⁾
<p>2</p>	Positioning range Y and U	ON	2 to 10 Vdc, 4 to 20 mA
		OFF	0 to 10 Vdc, 0 to 20 mA ¹⁾
<p>3</p>	Position feedback U	ON	Current (mA)
		OFF	Voltage (V) ¹⁾
<p>4</p>	Nominal flow rate C_V (k_{vs})	ON	63%
		OFF	100% ¹⁾

¹⁾ **Factory setting**

C_V (K_{VS}) reduction




For C_V (k_{VS}) reduction (DIP switch 4 in position ON), the stroke is limited to 63% mechanical stroke. 63% of full stroke then corresponds to an input/output signal of 10V.

If, in addition, the stroke is limited to 80%, for example, the minimum stroke is 0.63 × 0.8 = 0.50 of full stroke.

EA1512R1

Minimum stroke setting



With a suction throttle valve, it is essential that a minimum stroke limit be maintained to ensure compressor cooling and efficient oil return. This can be achieved with a re-injection valve, a bypass line across the valve, or a guaranteed minimum opening of the valve. The minimum stroke can be defined using the controller and control signal Y, or it can be set directly with potentiometer R_v.

EA1513R1

The factory setting is zero (mechanical stop in counterclockwise direction, CCW). The minimum stroke can be set by turning the potentiometer clockwise (CW) to a maximum of 80% C_V (k_{VS}).



CAUTION:

Do not, under any circumstances, use potentiometer R_v to limit the stroke on expansion applications. The valve must be able to fully close.

Forced control input ZC

		ZC – Function		
		No function	Fully open	Closed
Connections				
	Transfer			
function		<ul style="list-style-type: none"> • ZC not connected • Valve will follow the Y-signal • Minimum stroke set-ting with potentiometer R_v possible 	<ul style="list-style-type: none"> • ZC connected to G • Valve will fully open control path A → AB 	<ul style="list-style-type: none"> • ZC connected to G0 • Valve will close control path A → AB

EA1514R1

Signal priority

1. Forced control signal ZC
2. Signal input Y and/or minimum .stroke setting with potentiometer Rv possible.

Calibration

The printed circuit board of the MVL661... Series has a slot to facilitate calibration. To calibrate, insert a screwdriver in the slot so that the contacts inside are connected. As a result, the valve will first be fully closed and then fully opened.

Calibration matches the electronics to the valve mechanism.

During calibration, the green LED flashes for about 10 seconds; see Table 2.




Figure 1. Calibration Slot.

NOTE: MVL661... Refrigerant Valves are supplied fully calibrated.

When is calibration required?

Execute a calibration after replacing the electronics, when the red LED is lit or flashing or when the valve is leaking (at seat).

Table 2. Indication of Operating State.

LED	Indication	Operating State, Function	Remarks, Troubleshooting
Green	Lit	Control mode	Automatic operation; everything is OK.
	Flashing	Calibration in progress	Wait until calibration is finished (green or red LED will be lit).
Red	Lit	Calibration error Internal error	Recalibrate (operate button in opening 1x). Replace electronics module.
	Flashing	Main fault	Check electric main network (outside the frequency or voltage range).
Both	Dark	No power supply Electronics faulty	Check electric main network, check wiring Replace electronics module.

Connection type

NOTE: Four-wire connections are always preferred.

4-wire connection
 3-wire connection

Product Number	(VA)	(W)	(A)	Wire Gauge (AWG)		
				14	12	10
				Max. Cable Length Ft (m)		
MVL661...-	22	12	1.6 to 4A	213 (65)	361 (110)	525 (160)
MVL661...-	22	12	1.6 to 4A	65 (20)	115 (35)	164 (50)

S_{NA} = Nominal apparent power for selecting the transformer.

P_{med} = Typical power consumption.

I_F = Required slow fuse.

L = Max. cable length; with 4-wire connections, the max. permissible length of the separate 14 AWG (1.5 mm²) copper positioning signal wire is 656 ft (200 m).

1) All information at 24 Vac.

2) With 10 AWG (4 mm²) electrical wiring reduce wiring cross-section for connection inside valve to 12 AWG (2.5 mm²).

Sizing

For straightforward valve sizing, see *Application Examples*, beginning on page 12 for the relevant application.

For accurate valve sizing, Siemens Industry, Inc. recommends using the valve sizing software **Refrigeration VASP**.

NOTE: The refrigeration capacity Q_0 is calculated by multiplying the mass flow by the specific enthalpy differential found in the h, log p-chart for the relevant refrigerant. To help determine the refrigeration capacity more easily, see the selection chart provided for each application. With direct or indirect hot-gas bypass applications, the enthalpy differential of Q_c (the condenser capacity) must also be taken into account when calculating the refrigeration capacity.

If the evaporating and/or condensing temperatures are between the values shown in the tables, the refrigeration capacity can be determined with reasonable accuracy by linear interpolation. See *Application Examples*, beginning on page 12.

At the operating conditions given in the tables, the permissible differential pressure Δp_{max} across the valve is not considered.

If the evaporating temperature is raised by 1K, the refrigeration capacity increases by about 3%. If, by contrast, sub-cooling is increased by 1K, the refrigeration capacity increases by about 1 to 2% (this applies only to sub-cooling down to approximately 8K).

Engineering Notes

Depending on the application, additional installation instructions may need to be observed and appropriate safety devices (such as pressostats, full motor protection, and so on) fitted.




WARNING:

To prevent damage to the seal inside the valve insert, the plant must be vented on the low-pressure side following a pressure test (valve port AB), or the valve must be fully open during the pressure test and during venting (power supply connected and positioning signal at maximum or forced opening by G → ZC).

Expansion application

To prevent formation of flash gas on expansion applications, the velocity of the refrigerant in the fluid pipe may not exceed 3.5 ft/s (1 m/s). To assure this, the diameter of the fluid pipe must be greater than the nominal size of the valve, using reducing pieces for making the connections to the valve.



- a) The differential pressure over reduction must be less than half the differential pressure Δp_{FL} .
- b) The inlet path between diameter reduction and expansion valve inlet
 - Must straight for at least 2 feet (600 mm)
 - May not contain any valves




WARNING:


A filter/dryer must be mounted upstream of the expansion valve.
The valve is not explosion-proof.
It is not approved for use with ammonia (NH₃, R717).

Installation Notes

The valve should be mounted and commissioned by a qualified installer. The same applies to the replacement electronics and the configuration of the controller.



- The refrigerant valves can be mounted in any orientation above horizontal, but upright mounting is preferable.
- Arrange the pipework so that the valve is not located at a low point in the plant where oil can collect.
- The pipes should be fitted so that the alignment does not distort the valve connections. Fix the valve body so that that it cannot vibrate. Vibration can lead to burst connection pipes.
- Before soldering the pipes, ensure that the direction of flow through the valve is correct.
- The pipes must be soldered with care. To avoid dirt and the formation of scale (oxide), inert gas is recommended for soldering.



- The flame should be large enough to ensure that the junction heats up quickly and the valve does not get too hot.
- The flame should be directed away from the valve.
- During soldering, cool the valve with a wet cloth, for example, to ensure that it does not become too hot.
- Port B must be sealed off when a 2-port valve (AB → A) is used.

The valve is supplied complete with mounting instructions 74 319 0232 0.

Maintenance

The refrigerant valve is maintenance-free.

Repair

The valve cannot be repaired. Only the electronics (ASR61) can be replaced. If the valve is damaged or not functioning properly after changing the electronics, replace the entire unit.

Disposal

Do not dispose of the actuator or its electrical and electronic components with domestic waste.

The law may require special handling of certain components, or it may make sense from an ecological point of view.

NOTE: Observe all applicable local laws.

Warranty

Observe all application-specific technical data.

If you ignore specified limits, Siemens Industry, Inc./CPS Products will not assume any responsibility.

Specifications

Electrical

Power supply (extra low-voltage use only)	(SELV, PELV)
24 Vac	
Operating voltage	24 Vac ± 20%
Frequency	45 to 65 Hz
Typical power consumption	
P _{med}	12W
Standby	<1 W (valve fully closed)
Apparent power, S _{NA}	22 VA (for selecting the transformer)
Required fuse	Slow, 1.6 to 4A
24 Vdc	
Operating voltage	20 to 30 Vdc
Current draw	0.5A/2A (maximum)

Signal inputs

Control signal Y	0/2 to 10 Vdc, 0/4 to 20 mA,
Impedance	100K ohm/5nF
	240 ohm/5nF
Forced control ZC	
Input impedance	22K ohm
Closing the valve (ZC connected to G0)	<1 Vac; <0.8 Vdc
Opening the valve (ZC connected to G)	>6 Vac; >5 Vdc
No function (ZC not wired)	Positioning signal Y active

Signal outputs

Position feedback signal U	Voltage	0/2 to 10 Vdc; load resistance ≥ 500 Ω
	Current	0/4 to 20 mA; load resistance ≤ 500 Ω
Stroke measurement		Inductive
Nonlinearity		Accuracy ±3% full scale

Positioning time

Less than 1 second

Electrical connections	Cable entry glands	3 x \varnothing x 17 mm (for M16)	
	Min. wire size	20 AWG (0.75 mm ²)	
	Max. cable length	See <i>Connection Type</i>	
Functional data of valve	Nominal pressure	232 psi (PN 16)	
	Permissible Operating pressure ¹⁾	max. 652 psi (45 bar)	
	Max. differential pressure Δp_{max}	363 psi (25 bar)	
		1-1/4-inch (DN32): 29 psi (2 bar)	
	Valve characteristic (stroke vs. C_V or k_V)	Linear (to VDI/VDE2173)	
	Leakage rate (internally across seat)	Max. 0.002% C_V (K_V) or	
		Max. 1 NI/h gas at $\Delta p = 58$ psi (4 bar)	
		Shut/off function, like solenoid normally closed (NC) function	
	External seal	Hermetically sealed (fully welded, no static or dynamic seals)	
	Permissible media	Commonly used safety refrigerants (R22, R134a, R227ea, R404A, R407C, R410A, R422D, and so on) and R744 (CO ₂)	
		Not suitable for flammable refrigerants ² Not suitable for ammonia (R717). For refrigerants belonging to Fluid group 1, please contact your local Siemens representative.	
	Media temperature	-40°F to 248°F (-40°C to 120°C), Max. 284°F (140°C) for 10 min.	
	Stroke resolution $\Delta H/H_{100}$	1:1000 (H = Stroke)	
Hysteresis	Typically 3%		
Mode of operation	Modulating		
Position when de-energized	Control path A → AB closed		
Orientation:	Upright to horizontal		
Materials	Valve body and parts	Steel/CrNi steel	
	Seat/piston	CrNi steel/brass	
	Sealing disk	PTFE	
Pipe connections	Sleeves	Internally soldered, CrNi steel	
Ambient conditions	Temperature	Operation	-13°F to 131°F (-25°C to 55°C)
		Transport	-13°F to 158°F (-25°C to 70°C)
		Storage	23°F to 113°F (-5°C to 45°C)
	Humidity	Operation	10 to 100% rh
		Transport	< 95% rh
		Storage	5 to 95%
Miscellaneous	Weight	See Figure 13.	
	Dimensions	See Figure 13.	

Agency approvals	Degree of protection	IP65 as per EN 60529 ² Conforms to CE requirements UL Certified to UL 873 Cul Certified to CSA C22.2 No. 24 Conforms to RCM requirements PED 97/23/EC
	Electrical safety	EN 60730-1
	Protection class	Class III as per EN 60730
	Degree of pollution	Degree 2 as per EN 60730
	Vibration ³	EN 60068-2-6 5g acceleration, 10 to 150 Hz, 2.5 h (5g horizontal, max. 2g upright)
	Environmental compatibility	ISO 14001 (environment) ISO 9001 (quality) SN 36350 (environmentally-compatible products) RL 2002/95/EG (RoHS)
	Pressure accessories	As per article 1, section 2.1.4
	Fluid group 2	Without CE-marking as per article , section 3 (sound engineering practice)

- 1) To EN 12284 tested with 1,43 x operating pressure at 943 psi (65 bar).
- 2) At 18°F (45°C) < T_{amb} < 131°F (55°C) and 176°F (80°C) < T_{med} < 248°F (120°C) the valve must be installed on its side to avoid shortening the service life of the valve electronics.
- 3) In case of strong vibrations, use high-flex stranded wires for safety reasons.

Connection Terminals




Figure 2. Connection Terminals.

Connection Diagrams

Terminal assignment for controller with four-wire connection (preferred method)




Figure 3. Common Transformer.




Figure 4. Separate Transformer.

Terminal assignment for controller with three-wire connection




Figure 5. Common Transformer.




Figure 6. Separate Transformer.



Valve position indication (only if required). 0 to 10 Vdc → 0 to 100% volumetric flow 100.



Twisted pairs. If the 24 Vac power supply and the 0 to 10 Vdc/2 to 10 Vdc, 0 to 20 mA/4 to 20 mA) positioning signal are routed separately, the 24 Vac line does not need to be twisted.



WARNING:

Piping must be connected to potential earth.

Valve Sizing and Correction Factor

The applications and tables on the following pages are designed for help with selecting the valves. To select the correct valve, the following data is required:

- Application
 - Expansion (see *Use of the MVL661...as an expansion valve*)
 - Hot-gas (see *Use of the MVL661...as a hot-gas valve*)
 - Suction throttle (see *Use of the MVL661...as a suction throttle valve*)
- Refrigerant type
- Evaporating temperature t_0 °F (°C)
- Condensing temperature t_c °F (°C)
- Refrigeration capacity Q_0 (kW)

To calculate the nominal capacity, use the following formula:

- $k_{vs} [m^3/h] = Q_0 [kW] / K...*$
 - *K... for expansion = **KE**
 - for hot-gas = **KH**
 - for suction throttle = **KS**
- $CV = 1.156 \times kvs$
- The theoretical C_V (kv) value for the nominal refrigeration capacity of the plant should not be less than 50% of the C_V (kvs) value of the selected valve.
- For accurate valve sizing, we recommend using the valve selection program "Refrigeration VASP".


Application Examples

The application examples below reflect principles only. They do not include installation-specific details such as safety elements refrigerant collectors, and so on.

Use of the MVL661... as an expansion valve

- Typical control range is 20 to 100%.
- Increased capacity through better use of the evaporator.
- The use of two or more compressors or compressor stages significantly increases efficiency with low loads.
- Especially suitable for fluctuating condensing and evaporating pressures.
- For more information, see *Engineering Notes*.

Capacity optimization



- 1 = MVL661...-
- 2 = Evaporator
- 3 = Compressor
- 4 = Condenser

Electronic superheat control is achieved by using additional control equipment.

Application example

Refrigerant R407C; $Q_0 = 205$ kW; $t_0 = 25^\circ\text{F}$ (-5°C); $t_c = 95^\circ\text{F}$ (35°C)
 The correct C_V (k_{vs}) value for the MVL661...-.. valve needs to be determined.

The important section of table KE for R407C (see Table 4 or Table 5) is the area around the working point. The correction factor KE relevant to the working point should be determined by linear interpolation from the four guide values.

Note on interpolation

In practice, the KE, KH or KS value can be estimated because the theoretical C_V (k_{vs})-value ascertained will be rounded off by up to 30% to one of the ten available C_V (k_{vs})-values, allowing you to proceed directly at Step 4.

- Step 1: For $t_c = 95^\circ\text{F}$ (35°C), calculate the value for $t_o = 14^\circ\text{F}$ (-10°C) between values 68°F (20°C) and 104°F (40°C) in the table; result: **112**
- Step 2: For $t_c = 95^\circ\text{F}$ (35°C), calculate the value for $t_o = 32^\circ\text{F}$ (0°C) between values 68°F (20°C) and 104°F (40°C) in the table; result: **109**
- Step 3: For $t_o = 23^\circ\text{F}$ (-5°C), calculate the value for $t_c = 95^\circ\text{F}$ (35°C) between correction factors 112 and 109; calculated in steps 1 and 2; result: **111**
- Step 4: Calculate the theoretical C_V (k_{vs}) value; result: **2.14 (1.85 m³/h)**
- Step 5: Select the valve; the valve closest to the theoretical C_V (k_{vs}) value is the **MVL661.20-2.5**
- Step 6: Check that the theoretical C_V (k_{vs}) value is not less than 50% of the nominal C_V (k_{vs}) value

Table 3. Interpolation.

KE-R407C	$t_o = 14^\circ\text{F}$ (-10°C)	$t_o = 32^\circ\text{F}$ (0°C)	Interpolation at	$t_c = 95^\circ\text{F}$ (35°C)
$t_c = 68^\circ\text{F}$ (20°C)	108	85	$108 + [(113 - 108) \times (35 - 20)/(40 - 20)]$	112
$t_c = 95^\circ\text{F}$ (35°C)	<i>112</i>	<i>109</i>		
$t_c = 104^\circ\text{F}$ (40°C)	113	117	$85 + [(117 - 85) \times (35 - 20)/(40 - 20)]$	109

Interpolation at	$t_o = 23^\circ\text{F}$ (-5°C)
$112 + [(109 - 112) \times (-5 - 0)/(-10 - 0)]$	111

k_v theoretical = $205 \text{ kW}/111 = 1.85 \text{ m}^3/\text{h}$ ($C_V = k_{vs} \times 1.156 = 1.85 \times 1.156 = 2.14$)
Valve MVL661.20-2.5 is suitable, since: $1.85 \text{ m}^3/\text{h}/2.5 \text{ m}^3/\text{h} \times 100\% = 74\%$ ($> 50\%$)

Capacity control

- Refrigerant valve MVL661... for capacity control of a dry expansion evaporator. Suction pressure and temperature are monitored with a mechanical capacity controller and re-injection valve.
 - Typical control range 0 to 100%.
 - Energy-efficient operation with low loads.
 - Ideal control of temperature and dehumidification.




Figure 7. Dry Expansion Evaporator Capacity Control.

Capacity control,
continued

- Refrigerant valve MVL661... for capacity control of a chiller.
 - Typical control range 10 to 100%.
 - Energy-efficient operation with low loads.
 - Allows wide adjustment of condensing and evaporating temperatures.
 - Ideal for use with plate heat exchangers.
 - Very high degree of frost protection.




Figure 8. Chiller Capacity Control.

NOTE: A larger valve may be required for low load operation than is needed for full load conditions. To ensure that the selected valve will not be too small for low loads, sizing should take both possibilities into account.

Table 4. Correction Table, Expansion Valve (Fahrenheit).

t _c \t _o	R22					
	-40	-22	-4	14	32	50
32	82	68	37			
68	101	104	107	105	81	18
104	108	111	114	118	120	123
140	104	108	112	116	119	122

t _c \t _o	R134a					
	-40	-22	-4	14	32	50
32	27					
68	71	74	77	66	43	
104	74	78	81	85	89	92
140	67	72	76	81	85	89

t _c \t _o	R744					
	-40	-22	-4	14	32	50
-4	226	149				
32	262	264	241	166		
68	245	247	247	246	213	

t _c \t _o	R290 ¹⁾					
	-40	-22	-4	14	32	50
32	83	67	22			
68	104	109	113	107	80	
104	105	110	115	120	125	130
140	93	99	105	111	116	122

t _c \t _o	R401A					
	-40	-22	-4	14	32	50
32	31					
68	80	83	85	72	46	
104	87	90	94	97	101	102
140	85	89	94	98	102	106

t _c \t _o	R402A					
	-40	-22	-4	14	32	50
32	73	69	50			
68	77	81	85	88	74	35
104	71	75	80	84	88	91
140	50	55	60	65	69	74

t _c \t _o	R404A					
	-40	-22	-4	14	32	50
32	69	63	44			
68	70	74	78	81	68	30
104	61	65	70	74	78	81
140	36	41	46	51	55	59

t _c \t _o	R407A					
	-40	-22	-4	14	32	50
32	79	67	40			
68	91	95	98	102	82	30
104	89	94	98	102	106	110
140	72	77	82	87	92	96

t _c \t _o	R407B					
	-40	-22	-4	14	32	50
32	72	66	45			
68	77	80	84	88	75	34
104	69	74	78	83	87	91
140	46	51	56	61	66	70

t _c \t _o	R407C					
	-40	-22	-4	14	32	50
32	79	65	31			
68	98	101	105	108	85	21
104	100	104	109	113	117	121
140	87	93	98	103	108	113

t _c \t _o	R410A					
	-40	-22	-4	14	32	50
32	116	117	91	12		
68	125	130	133	137	120	69
104	119	124	129	133	137	140
140	90	96	101	106	110	114

t _c \t _o	R410B					
	-40	-22	-4	14	32	50
32	112	112	87	11		
68	122	126	129	132	115	66
104	119	124	128	131	134	137
140	98	103	108	112	115	118

t _c \t _o	R507					
	-40	-22	-4	14	32	50
32	72	66	47			
68	78	81	83	86	71	33
104	74	78	81	84	87	90
140	53	57	61	64	68	71

t _c \t _o	R1270 ¹⁾					
	-40	-22	-4	14	32	50
32	109	93	59			
68	122	126	130	129	101	31
104	122	127	133	138	142	147
140	108	115	121	127	132	138

- With superheat = 6 K With subcooling = 2 K Δp upstream of evaporator = 23 psi (1.6 bar)
- Δp condenser = 4.4 psi (0.3 bar) Δp evaporator = 4.4 psi (0.3 bar)
- ¹⁾ For refrigerants belonging to Fluid group 1, please contact your local Siemens representative.

Table 5. Correction Table, Expansion Valve (Celsius).

$t_c \backslash t_o$	R22					
	-40	-30	-20	-10	0	10
00	82	68	37			
20	101	104	107	105	81	18
40	108	111	114	118	120	123
60	104	108	112	116	119	122

$t_c \backslash t_o$	R134a					
	-40	-30	-20	-10	0	10
00	27					
20	71	74	77	66	43	
40	74	78	81	85	89	92
60	67	72	76	81	85	89

$t_c \backslash t_o$	R744					
	-40	-30	-20	-10	0	10
-20	226	149				
00	262	264	241	166		
20	245	247	247	246	213	

$t_c \backslash t_o$	R290 ¹⁾					
	-40	-30	-20	-10	0	10
00	83	67	22			
20	104	109	113	107	80	
40	105	110	115	120	125	130
60	93	99	105	111	116	122

$t_c \backslash t_o$	R401A					
	-40	-30	-20	-10	0	10
00	31					
20	80	83	85	72	46	
40	87	90	94	97	101	102
60	85	89	94	98	102	106

$t_c \backslash t_o$	R402A					
	-40	-30	-20	-10	0	10
00	73	69	50			
20	77	81	85	88	74	35
40	71	75	80	84	88	91
60	50	55	60	65	69	74

$t_c \backslash t_o$	R404A					
	-40	-30	-20	-10	0	10
00	69	63	44			
20	70	74	78	81	68	30
40	61	65	70	74	78	81
60	36	41	46	51	55	59

$t_c \backslash t_o$	R407A					
	-40	-30	-20	-10	0	10
00	79	67	40			
20	91	95	98	102	82	30
40	89	94	98	102	106	110
60	72	77	82	87	92	96

$t_c \backslash t_o$	R407B					
	-40	-30	-20	-10	0	10
00	72	66	45			
20	77	80	84	88	75	34
40	69	74	78	83	87	91
60	46	51	56	61	66	70

$t_c \backslash t_o$	R407C					
	-40	-30	-20	-10	0	10
00	79	65	31			
20	98	101	105	108	85	21
40	100	104	109	113	117	121
60	87	93	98	103	108	113

$t_c \backslash t_o$	R410A					
	-40	-30	-20	-10	0	10
00	116	117	91	12		
20	125	130	133	137	120	69
40	119	124	129	133	137	140
60	90	96	101	106	110	114

$t_c \backslash t_o$	R410B					
	-40	-30	-20	-10	0	10
00	112	112	87	11		
20	122	126	129	132	115	66
40	119	124	128	131	134	137
60	98	103	108	112	115	118

$t_c \backslash t_o$	R507					
	-40	-30	-20	-10	0	10
00	72	66	47			
20	78	81	83	86	71	33
40	74	78	81	84	87	90
60	53	57	61	64	68	71

$t_c \backslash t_o$	R1270 ¹⁾					
	-40	-30	-20	-10	0	10
00	109	93	59			
20	122	126	130	129	101	31
40	122	127	133	138	142	147
60	108	115	121	127	132	138


- With superheat = 6 K With sub-cooling = 2 K Δp upstream of evaporator = 23 psi (1.6 bar)
- Δp condenser = 4.4 psi (0.3 bar) Δp evaporator = 4.4 psi (0.3 bar)

¹⁾ For refrigerants belonging to Fluid group 1, please contact your local Siemens representative.

Use of the MVL661...
as a hot-gas valve

The control valve throttles the capacity of a compressor stage. The hot gas passes directly to the evaporator, and allows capacity control in the range from 100% down to approximately 0%.

Indirect hot-gas bypass
application



Suitable for use in large refrigeration systems in air conditioning plant, to prevent unacceptable temperature fluctuations between the compressor stages.

Figure 9. Indirect Hot-Gas Bypass Application.

Application example

With low loads, the evaporating and condensing pressures can fluctuate depending on the type of pressure control. In such cases, evaporating pressure increases and condensing pressure decreases. Due to the reduction in differential pressure across the fully open valve, the volumetric flow rate will drop since the valve is undersized. This is why the effective pressures must be taken into account when sizing the valve for low loads.

Refrigerant R507; 3 compressor stages; $Q_0 = 75 \text{ kW}$; $t_0 = 39^\circ\text{F}$ (4°C); $t_c = 104^\circ\text{F}$ (40°C).
Part load Q_0 per stage = 28 kW ; $t_0 = 39^\circ\text{F}$ (4°C); $t_c = 73.4^\circ\text{F}$ (23°C).

KH-R507	$t_0 = 32^\circ\text{F}$ (0°C)	$t_0 = 50^\circ\text{F}$ (10°C)
$t_c = 36^\circ\text{F}$ (2°C)	14.4	9.0
$t_c = 73^\circ\text{F}$ (23°C)	15.6	11.0
$t_c = 104^\circ\text{F}$ (40°C)	22.4	22.0

Interpolation at	$t_c = 73.4^\circ\text{F}$ (23°C)
$14.4 + [(22.4 - 14.4) \times (23 - 20)/(40 - 20)]$	15.6
$9.0 + [(22.0 - 9.0) \times (23 - 20)/(40 - 20)]$	11.0

Interpolation at	$t_0 = 39^\circ\text{F}$ (4°C)
$15.6 + [(11.0 - 15.6) \times (4 - 0)/(10 - 0)]$	13.8


k_{vs} theoretical = $28 \text{ kW}/13.8 = 2.03 \text{ m}^3/\text{h}$ ($C_v = k_{vs} \times 1.156 = 2.03 \times 1.156 = 2.35$)

Valve MVL661.20-2.5 is suitable, since: $C_v = k_{vs} \times 1.156 = 2.03 \times 1.156 = 2.35$

$(2.03 \text{ m}^3/\text{h} / 2.5 \text{ m}^3/\text{h} \times 100\% = 81\% [> 50\%])$

Direct hot-gas bypass
application

The control valve throttles the capacity of one compressor stage. The gas is fed to the suction side of the compressor and then cooled using a reinjection valve. Capacity control ranges from 100% down to approximately 10%.



Suitable for large refrigeration systems in air conditioning applications with several compressors or compressor stages, and where the evaporator and compressor are some distance apart (attention must be paid to the oil return).

Figure 10. Direct Hot-Gas Bypass Application.

Table 6. Correction Table, Hot Gas Valve (Fahrenheit).

		R22					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		8.9	8.4	6.3			
68		15.3	15.1	14.8	14.6	13.2	6.5
104		24.2	23.7	23.2	22.8	22.4	22.1
140		35.7	34.7	33.8	33.0	32.3	31.7

		R134a					
$t_c \setminus t_o$		-40	-22	-4	-14	32	50
32		4.5					
68		9.8	9.6	9.5	9.2	7.4	
104		15.9	15.6	15.3	15.1	14.9	14.7
140		23.8	23.2	22.7	22.3	21.9	21.6

		R744					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
-4		38.1	30.5				
32		60.9	59.8	58.1	47.1		
68		87.3	84.9	82.5	80.2	76.1	

		R290 ¹⁾					
$t_c \setminus t_o$		-40	-22	-4	-14	32	50
32		10.9	10.0	6.5			
68		18.0	17.7	17.4	17.1	15.0	
104		27.3	26.7	26.2	25.8	25.4	25.1
140		38.2	37.2	36.4	35.7	35.1	34.5

		R401A					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		4.7					
68		10.2	10.0	9.9	9.5	7.6	
104		16.9	16.6	16.2	16.0	15.8	15.6
140		25.9	25.2	24.6	24.1	23.7	23.3

		R402A					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		9.7	9.5	8.3			
68		15.9	15.7	15.4	15.2	14.5	9.3
104		23.7	23.2	22.7	22.4	22.0	21.7
140		31.5	30.7	29.9	29.2	28.7	28.1

		R404A					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		9.4	9.2	7.8			
68		15.2	15.0	14.8	14.6	13.9	8.6
104		22.3	21.8	21.5	21.1	20.9	20.6
140		28.8	28.0	27.4	26.8	26.4	25.9

		R407A					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		8.9	8.6	6.7			
68		15.7	15.4	15.2	15.0	14.1	8.0
104		24.9	24.4	23.9	23.5	23.1	22.8
140		35.9	34.9	34.0	33.2	32.6	32.0

		R407B					
$t_c \setminus t_o$		-40	-22	-4	-14	32	50
32		9.0	8.8	7.4			
68		15.3	15.1	14.8	14.7	14.0	8.8
104		23.3	22.8	22.4	22.0	21.7	21.5
140		31.6	30.7	30.0	29.3	28.8	28.3

		R407C					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		8.6	8.1	5.9			
68		15.3	15.0	14.8	14.6	13.6	7.0
104		24.7	24.2	23.7	23.3	22.9	22.6
140		36.3	35.3	34.4	33.6	33.0	32.4

		R410A					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		14.5	14.3	13.2	6.2		
68		24.2	23.7	23.3	23.0	22.1	15.9
104		36.8	35.9	35.1	34.4	33.7	33.1
140		50.0	48.5	47.2	46.0	44.9	43.8

		R410B					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		14.3	14.1	12.9	6.1		
68		23.8	23.3	22.9	22.5	21.6	15.5
104		36.5	35.6	34.7	33.9	33.2	32.5
140		50.7	49.1	47.7	46.4	45.2	44.0

		R507					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		9.8	9.5	8.1			
68		16.1	15.8	15.5	15.3	14.4	9.0
104		24.5	23.8	23.3	22.8	22.4	22.0
140		33.1	31.8	30.7	29.8	29.0	28.3

		R1270 ¹⁾					
$t_c \setminus t_o$		-40	-22	-4	14	32	50
32		13.5	13.0	10.3			
68		22.0	21.6	21.2	20.9	19.0	9.9
104		33.0	32.2	31.6	31.1	30.6	30.1
140		46.1	44.8	43.8	42.8	41.9	41.2

- With superheat = 6 K With subcooling = 2 K Δp upstream of evaporator = 23 psi (1.6 bar)
 - Δp condenser = 4.4 psi (0.3 bar) Δp evaporator = 4.4 psi (0.3 bar)
- ¹⁾ For refrigerants belonging to Fluid group 1, please contact your local Siemens representative.

Table 7. Correction Table, Hot Gas Valve (Celsius).

$t_c \setminus t_o$	R22					
	-40	-30	-20	-10	0	10
00	8.9	8.4	6.3			
20	15.3	15.1	14.8	14.6	13.2	6.5
40	24.2	23.7	23.2	22.8	22.4	22.1
60	35.7	34.7	33.8	33.0	32.3	31.7

$t_c \setminus t_o$	R134a					
	-40	-30	-20	-10	0	10
00	4.5					
20	9.8	9.6	9.5	9.2	7.4	
40	15.9	15.6	15.3	15.1	14.9	14.7
60	23.8	23.2	22.7	22.3	21.9	21.6

$t_c \setminus t_o$	R744					
	-40	-30	-20	-10	0	10
-20	38.1	30.5				
00	60.9	59.8	58.1	47.1		
20	87.3	84.9	82.5	80.2	76.1	

$t_c \setminus t_o$	R290 ¹⁾					
	-40	-30	-20	-10	0	10
00	10.9	10.0	6.5			
20	18.0	17.7	17.4	17.1	15.0	
40	27.3	26.7	26.2	25.8	25.4	25.1
60	38.2	37.2	36.4	35.7	35.1	34.5

$t_c \setminus t_o$	R401A					
	-40	-30	-20	-10	0	10
00	4.7					
20	10.2	10.0	9.9	9.5	7.6	
40	16.9	16.6	16.2	16.0	15.8	15.6
60	25.9	25.2	24.6	24.1	23.7	23.3

$t_c \setminus t_o$	R402A					
	-40	-30	-20	-10	0	10
00	9.7	9.5	8.3			
20	15.9	15.7	15.4	15.2	14.5	9.3
40	23.7	23.2	22.7	22.4	22.0	21.7
60	31.5	30.7	29.9	29.2	28.7	28.1

$t_c \setminus t_o$	R404A					
	-40	-30	-20	-10	0	10
00	9.4	9.2	7.8			
20	15.2	15.0	14.8	14.6	13.9	8.6
40	22.3	21.8	21.5	21.1	20.9	20.6
60	28.8	28.0	27.4	26.8	26.4	25.9

$t_c \setminus t_o$	R407A					
	-40	-30	-20	-10	0	10
00	8.9	8.6	6.7			
20	15.7	15.4	15.2	15.0	14.1	8.0
40	24.9	24.4	23.9	23.5	23.1	22.8
60	35.9	34.9	34.0	33.2	32.6	32.0

$t_c \setminus t_o$	R407B					
	-40	-30	-20	-10	0	10
00	9.0	8.8	7.4			
20	15.3	15.1	14.8	14.7	14.0	8.8
40	23.3	22.8	22.4	22.0	21.7	21.5
60	31.6	30.7	30.0	29.3	28.8	28.3

$t_c \setminus t_o$	R407C					
	-40	-30	-20	-10	0	10
00	8.6	8.1	5.9			
20	15.3	15.0	14.8	14.6	13.6	7.0
40	24.7	24.2	23.7	23.3	22.9	22.6
60	36.3	35.3	34.4	33.6	33.0	32.4

$t_c \setminus t_o$	R410A					
	-40	-30	-20	-10	0	10
00	14.5	14.3	13.2	6.2		
20	24.2	23.7	23.3	23.0	22.1	15.9
40	36.8	35.9	35.1	34.4	33.7	33.1
60	50.0	48.5	47.2	46.0	44.9	43.8

$t_c \setminus t_o$	R410B					
	-40	-30	-20	-10	0	10
00	14.3	14.1	12.9	6.1		
20	23.8	23.3	22.9	22.5	21.6	15.5
40	36.5	35.6	34.7	33.9	33.2	32.5
60	50.7	49.1	47.7	46.4	45.2	44.0

$t_c \setminus t_o$	R507					
	-40	-30	-20	-10	0	10
00	9.8	9.5	8.1			
20	16.1	15.8	15.5	15.3	14.4	9.0
40	24.5	23.8	23.3	22.8	22.4	22.0
60	33.1	31.8	30.7	29.8	29.0	28.3

$t_c \setminus t_o$	R1270 ¹⁾					
	-40	-30	-20	-10	0	10
00	13.5	13.0	10.3			
20	22.0	21.6	21.2	20.9	19.0	9.9
40	33.0	32.2	31.6	31.1	30.6	30.1
60	46.1	44.8	43.8	42.8	41.9	41.2

- With superheat = 6 K With subcooling = 2 K Δp upstream of evaporator = 23 psi (1.6 bar)
 - Δp condenser = 4.4 psi (0.3 bar) Δp evaporator = 4.4 psi (0.3 bar)
- ¹⁾ For refrigerants belonging to Fluid group 1, please contact your local Siemens representative.

Use of the MVL661...
 as a suction throttle
 valve




Figure 11. Suction Throttle Valve Application.

Typical control range 50 to 100%.

Minimum stroke limit control:
 To ensure optimum cooling of the compressor, either a capacity controller must be provided for the compressor, or a minimum stroke must be set using the valve electronics.

The minimum stroke is limited to a maximum of 80%. At zero load, the minimum stroke must be sufficient to ensure that the minimum gas velocity in the suction line is > 0.7 m/s and that the compressor is adequately cooled.

As the control valve closes, the evaporating temperature rises, and the air cooling effect decreases continuously. The electronic control system provides demand-based cooling without unwanted dehumidification and costly retreatment of the air.

The pressure at the compressor inlet falls and the power consumption of the compressor is reduced. The energy savings to be anticipated with low loads can be determined from the compressor selection chart (power consumption at minimum permissible suction pressure). Compressor energy savings of up to 40% can be achieved.

The recommended differential pressure Δp_{V100} across the fully open control valve is between 2.2 psi (0.15 bar) < Δp_{V100} < 7.25 psi (0.5 bar).

Application example

Refrigerant R134A; $Q_0 = 9.5 \text{ kW}$; $t_0 = 39^\circ\text{F}$ (4°C); $t_c = 104^\circ\text{F}$ (40°C);
 Differential pressure across MVL661: $\Delta p_{V100} = 3.6 \text{ psi}$ (0.25 bar)

In this application example, t_0 , t_c and Δp_{V100} are to be interpolated.

KS-R134a	$t_0 = 32^\circ\text{F}$ (0°C)	$t_0 = 50^\circ\text{F}$ (10°C)	Interpolation at $t_0 = 39^\circ\text{F}$ (4°C)	
0.15/20	2.2	2.7	$2.2 + [(2.7 - 2.2) \times (4 - 0)/(10 - 0)]$	2.4
0.15/50	1.7	2.1	$1.7 + [(2.1 - 1.7) \times (4 - 0)/(10 - 0)]$	1.9
0.45/20	3.6	4.5	$3.6 + [(4.5 - 3.6) \times (4 - 0)/(10 - 0)]$	4.0
0.45/50	2.7	3.4	$2.7 + [(3.4 - 2.7) \times (4 - 0)/(10 - 0)]$	3.0

$t_0 = 39^\circ\text{F}$ (4°C)	$t_c = 68^\circ\text{F}$ (20°C)	$t_c = 122^\circ\text{F}$ (50°C)	Interpolation at $t_c = 104^\circ\text{F}$ (40°C)	
$\Delta p_{V100} 0.15$	2.4	1.9	$2.4 + [(1.9 - 2.4) \times (40 - 20)/(50 - 20)]$	2.1
$\Delta p_{V100} 0.45$	4.0	3.0	$4.0 + [(3.0 - 4.0) \times (40 - 20)/(50 - 20)]$	3.3

$t_c = 104^\circ\text{F}$ (40°C)	Δp_{V100} 2.2 psi (0.15 bar)	Δp_{V100} 6.5 psi (0.45 bar)	Interpolation at $\Delta p_{V100} 3.6 \text{ psi}$ (0.25 bar)	
	2.1	3.3	$2.1 + [(3.3 - 2.1) \times (0.25 - 0.15)/(0.45 - 0.15)]$	2.5

$k_{vs} \text{ theoretical} = 9.5 \text{ kW} / 2.5 = 3.8 \text{ m}^3/\text{h}$ ($CV = k_{vs} \times 1.156 = 3.8 \times 1.156 = 4.4$).

Valve MVL661.25-6.3 is suitable, since $3.8 \text{ m}^3/\text{h} / 6.3 \text{ m}^3/\text{h} \times 10\% = 60\%$ (> 50%).

It is recommended that the C_V (k_{vs}) value be set to 63% = 4.6 ($4 \text{ m}^3/\text{h}$).




Figure 12.

Typical control range 10 to 100%.

The capacity controller ensures that the compressor is adequately cooled, making it unnecessary to set a minimum stroke in the refrigerant valve.

Table 8. Correction Table, Suction Throttle Valve (psi/Fahrenheit).

t_c	R22					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	1.2	1.5	1.9	2.4	2.9	3.4
2.2/122	0.9	1.2	1.5	1.9	2.3	2.7
6.5/68	1.5	2.3	3.0	3.9	4.8	5.7
6.5/122	1.2	1.8	2.4	3.0	3.8	4.6

t_c	R134a					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	0.7	1.0	1.4	1.8	2.2	2.7
2.2/122	0.5	0.7	1.0	1.3	1.7	2.1
6.5/68	0.7	1.2	1.9	2.7	3.6	4.5
6.5/122	0.5	0.9	1.4	2.0	2.7	3.4

t_c	R152A ¹⁾					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	0.9	1.3	1.7	2.2	2.7	3.3
2.2/122	0.7	1.0	1.4	1.7	2.2	2.7
6.5/68	1.0	1.5	2.4	3.3	4.3	5.3
6.5/122	0.7	1.2	1.9	2.6	3.5	4.4

t_c	R290 ¹⁾					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	1.5	1.9	2.4	3.0	3.6	4.3
2.2/122	1.0	1.4	1.8	2.2	2.7	3.3
6.5/68	2.0	2.8	3.8	4.8	6.0	7.2
6.5/122	1.4	2.1	2.8	3.6	4.5	5.5

t_c	R401A					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	0.8	1.1	1.5	1.9	2.3	2.9
2.2/122	0.6	0.8	1.1	1.5	1.8	2.3
6.5/68	0.8	1.3	2.1	2.9	3.7	4.7
6.5/122	0.6	1.0	1.6	2.3	3.0	3.7

t_c	R402A					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	1.1	1.4	1.8	2.2	2.7	3.3
2.2/122	0.7	0.9	1.2	1.5	1.8	2.3
6.5/68	1.5	2.2	2.9	3.7	4.6	5.6
6.5/122	0.9	1.4	1.9	2.4	3.1	3.8

t_c	R404A					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	1.0	1.3	1.7	2.2	2.7	3.3
2.2/122	0.6	0.8	1.1	1.4	1.7	2.1
6.5/68	1.4	2.1	2.8	3.6	4.5	5.5
6.5/122	0.8	1.2	1.7	2.3	2.9	3.6

t_c	R407A					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	1.0	1.4	1.8	2.3	2.9	3.5
2.2/122	0.7	1.0	1.3	1.6	2.1	2.6
6.5/68	1.3	2.0	2.9	3.8	4.7	5.9
6.5/122	0.9	1.4	2.0	2.7	3.4	4.3

t_c	R407B					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	1.0	1.3	1.7	2.2	2.7	3.3
2.2/122	0.6	0.8	1.1	1.4	1.8	2.2
6.5/68	1.3	2.0	2.7	3.5	4.5	5.5
6.5/122	0.8	1.2	1.7	2.3	3.0	3.8

t_c	R407C					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	1.0	1.4	1.8	2.3	2.9	3.5
2.2/122	0.7	1.0	1.3	1.7	2.1	2.6
6.5/68	1.3	2.0	2.8	3.8	4.8	5.9
6.5/122	0.9	1.4	2.1	2.8	3.5	4.4

t_c	R410A					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	1.5	2.0	2.5	3.0	3.6	4.4
2.2/122	1.0	1.3	1.7	2.1	2.6	3.1
6.5/68	2.3	3.1	4.0	5.0	6.1	7.4
6.5/122	1.6	2.1	2.8	3.5	4.4	5.3

t_c	R410B					
	$\Delta p_{v100} \setminus t_o$	-40	-22	-4	14	32
2.2/68	1.5	1.9	2.4	2.9	3.6	4.2
2.2/122	1.0	1.3	1.7	2.1	2.6	3.1
6.5/68	2.3	3.1	3.9	4.9	6.0	7.2
6.5/122	1.6	2.1	2.8	3.5	4.3	5.2

- With superheat = 6 K With sub-cooling = 2 K Δp upstream of evaporator = 23 psi (1.6 bar)
- Δp condenser = 4.4 psi (0.3 bar) Δp evaporator = 4.4 psi (0.3 bar)

¹⁾For refrigerants belonging to Fluid group 1, please contact your local Siemens representative.

Table 9. Correction Table, Suction Throttle Valve (bar/Celsius).

t_c	R22					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	1.2	1.5	1.9	2.4	2.9	3.4
0.15/50	0.9	1.2	1.5	1.9	2.3	2.7
0.45/20	1.5	2.3	3.0	3.9	4.8	5.7
0.45/50	1.2	1.8	2.4	3.0	3.8	4.6

t_c	R134a					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	0.7	1.0	1.4	1.8	2.2	2.7
0.15/50	0.5	0.7	1.0	1.3	1.7	2.1
0.45/20	0.7	1.2	1.9	2.7	3.6	4.5
0.45/50	0.5	0.9	1.4	2.0	2.7	3.4

t_c	R152A ¹⁾					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	0.9	1.3	1.7	2.2	2.7	3.3
0.15/50	0.7	1.0	1.4	1.7	2.2	2.7
0.45/20	1.0	1.5	2.4	3.3	4.3	5.3
0.45/50	0.7	1.2	1.9	2.6	3.5	4.4

t_c	R290 ¹⁾					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	1.5	1.9	2.4	3.0	3.6	4.3
0.15/50	1.0	1.4	1.8	2.2	2.7	3.3
0.45/20	2.0	2.8	3.8	4.8	6.0	7.2
0.45/50	1.4	2.1	2.8	3.6	4.5	5.5

t_c	R401A					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	0.8	1.1	1.5	1.9	2.3	2.9
0.15/50	0.6	0.8	1.1	1.5	1.8	2.3
0.45/20	0.8	1.3	2.1	2.9	3.7	4.7
0.45/50	0.6	1.0	1.6	2.3	3.0	3.7

t_c	R402A					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	1.1	1.4	1.8	2.2	2.7	3.3
0.15/50	0.7	0.9	1.2	1.5	1.8	2.3
0.45/20	1.5	2.2	2.9	3.7	4.6	5.6
0.45/50	0.9	1.4	1.9	2.4	3.1	3.8

t_c	R404A					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	1.0	1.3	1.7	2.2	2.7	3.3
0.15/50	0.6	0.8	1.1	1.4	1.7	2.1
0.45/20	1.4	2.1	2.8	3.6	4.5	5.5
0.45/50	0.8	1.2	1.7	2.3	2.9	3.6

t_c	R407A					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	1.0	1.4	1.8	2.3	2.9	3.5
0.15/50	0.7	1.0	1.3	1.6	2.1	2.6
0.45/20	1.3	2.0	2.9	3.8	4.7	5.9
0.45/50	0.9	1.4	2.0	2.7	3.4	4.3

t_c	R407B					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	1.0	1.3	1.7	2.2	2.7	3.3
0.15/50	0.6	0.8	1.1	1.4	1.8	2.2
0.45/20	1.3	2.0	2.7	3.5	4.5	5.5
0.45/50	0.8	1.2	1.7	2.3	3.0	3.8


t_c	R407C					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	1.0	1.4	1.8	2.3	2.9	3.5
0.15/50	0.7	1.0	1.3	1.7	2.1	2.6
0.45/20	1.3	2.0	2.8	3.8	4.8	5.9
0.45/50	0.9	1.4	2.1	2.8	3.5	4.4

t_c	R410A					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	1.5	2.0	2.5	3.0	3.6	4.4
0.15/50	1.0	1.3	1.7	2.1	2.6	3.1
0.45/20	2.3	3.1	4.0	5.0	6.1	7.4
0.45/50	1.6	2.1	2.8	3.5	4.4	5.3

t_c	R410B					
	$\Delta p_{v100} \setminus t_o$	-40	-30	-20	-10	0
0.15/20	1.5	1.9	2.4	2.9	3.6	4.2
0.15/50	1.0	1.3	1.7	2.1	2.6	3.1
0.45/20	2.3	3.1	3.9	4.9	6.0	7.2
0.45/50	1.6	2.1	2.8	3.5	4.3	5.2

- With superheat = 6 K With subcooling = 2 K Δp upstream of evaporator = 23 psi (1.6 bar)
 - Δp condenser = 4.4 psi (0.3 bar) Δp evaporator = 4.4 psi (0.3 bar)
- ¹⁾ For refrigerants belonging to Fluid group 1, please contact your local Siemens representative.

Dimensions



Product Number	Line Size	D	L	H1	H2	H3	H4	Weight lb (kg)
MVL661.15-0.4	1/2	5/8	5.51 (140)	1.73 (44)	1.42 (36)	4.45 (113)	6.30 (160)	9.7 (4.4)
MVL661.15-1.0	1/2	5/8	5.51 (140)	1.73 (44)	1.42 (36)	4.45 (113)		9.7 (4.4)
MVL661.20-2.5	3/4	7/8	5.90 (150)	1.61 (41)	1.61 (41)	4.69 (119)		9.9 (4.5)
MVL661.25-6.3	1	1-1/8	6.30 (160)	1.57 (40)	1.85 (47)	4.96 (126)		10.1 (4.6)
MVL661.32-12	1-1/2	1-3/8	7.5 (190)	1.69 (43)	2.13 (54)	5.59 (142)		13.4 (6.1)

DN Nominal size

D Pipe connections (inch), internal dimension

NOTE: Weight includes packaging.

Figure 13. Dimensions in Inches (Millimeters).

Information in this publication is based on current specifications. The company reserves the right to make changes in specifications and models as design improvements are introduced. Product or company names mentioned herein may be trademarks of their respective owners.
 © 2016 Siemens Industry, Inc.