



VVF47..



VXF47..

ACVATIX™

2-port and 3-port seat valves PN16, flanged connections

VVF47..
VXF47..

- Grey cast iron EN-GJL-250
- DN 50...150
- k_{vs} 40...315 m³/h
- Can be equipped with SBX.., SBV.. actuators

Use

For use in heating, ventilating and air conditioning systems as a control valve.
For closed circuits only.

Type summary

Product No.	Stock No.	DN	k_{vs} [m ³ /h]	S_v
VVF47.50	S55220-V106	50	40	> 50
VVF47.65	S55220-V107	65	63	
VVF47.80	S55220-V108	80	100	
VVF47.100	S55220-V109	100	160	
VVF47.125	S55220-V110	125	250	
VVF47.150	S55220-V111	150	315	
VXF47.50	S55220-V100	50	40	> 50
VXF47.65	S55220-V101	65	63	
VXF47.80	S55220-V102	80	100	
VXF47.100	S55220-V103	100	160	
VXF47.125	S55220-V104	125	250	
VXF47.150	S55220-V105	150	315	

DN = Nominal size

k_{vs} = Nominal flow rate of cold water (5...30 °C) through the fully open valve (H_{100}) by a differential pressure of 100 kPa (1 bar)

S_v = Rangeability k_{vs}/k_{vr}

k_{vr} = Smallest k_v value, at which the flow characteristic tolerances can still be maintained, by a differential pressure of 100 kPa (1 bar)

Ordering

Example

Product number	Stock number	Designation	Quantity
VVF47.50	S55220-V106	2-port seat valve PN16 with flanged connection	1

Delivery

Valves and actuators are packed and supplied separately.

The valves are supplied without counter-flanges and without flange gaskets.

Error! Reference source not found.,

See "Error! Reference source not found.", page Error! Bookmark not defined..

Equipment combinations

Valves	Actuators			
	SBX..		SBV..	
	Δp_s	Δp_{max}	Δp_s	Δp_{max}
	kPa		kPa	
VVF47.50	300	300		
VVF47.65	175	175	400	300
VVF47.80	100	100	250	250
VVF47.100			400	300
VVF47.125			400	300
VVF47.150			400	300
VXF47.50		300		
VXF47.65		175		300
VXF47.80		100		250
VXF47.100				200
VXF47.125				100
VXF47.150				75

Δp_{max} = Maximum permissible differential pressure across the valve, valid for the entire actuating range of the motorized valve


Δp_s = Maximum permissible differential pressure at which the motorized valve will close securely against the pressure (close off pressure)

Actuator overview

Type	Operating voltage	Positioning signal	Feedback signal	Positioning time (s)	Positioning force (N)	Datasheet
SBX31	AC 230 V	3-position	No	120	800	N4519
SBX81	AC 24 V	3-position	No	120	800	
SBX61	AC 24 V	DC 0...10 V	DC 0...10 V	120	800	
SBX151.00	AC 24 V	4...20 mA	4...20 mA	120	800	
SBV31	AC 230 V	3-position	No	180	1600	
SBV81	AC 24 V	3-position	No	180	1600	
SBV61	AC 24 V	DC 0...10 V	DC 0...10 V	180	1600	
SBV151.00	AC 24 V	4...20 mA	4...20 mA	180	1600	

Technical design / mechanical design

Valve cross section




Guided plug integrated with the valve stem. The seats are machined in the valve body.

Schematic representation, design variations are possible.

The 2-port valve does not become a 3-port valve by removing the blank flange.


Flow diagram

VVF47..



4419Z04


VXF47..



4419Z03

- Δp_{max} = Maximum permissible differential pressure across the valve's control path, valid for the entire actuating range of the motorized valve
- Δp_{V100} = Differential pressure across the fully open valve by a volume flow V_{100}
- V_{100} = Volumetric flow through the fully open valve (H_{100})
- 100 kPa = 1 bar \approx 10 mWC
- 1 m^3/h = 0.278 l/s water at 20 °C


Valve flow characteristic
VVF47



0...30%: linear
30...100%: equal-percentage
 $n_{gl} = 3$ as per VDI/VDE 2173


For valve k_{vs} -values 100 and 160 m³/h, the characteristic is optimized for maximum volumetric flow k_{V100} at 80 %...100 %

VVF47.125-250
VVF47.150-315



0...100%: Linear

VXF47



Throughport A-AB

0...30 %: linear
30...100 %: equal-percentage
 $n_{gl} = 3$ as per VDI/VDE 2173

For valve k_{vs} -values ≥ 100 m³/h, the characteristic is optimized for maximum volumetric flow k_{V100} at 80%...100%

Bypass B-AB


0...100 %: linear

Cavitation


Cavitation accelerates wear on the plug and seat, and also results in undesirable noise. Cavitation can be avoided by not exceeding the differential pressure shown in the flow diagram on page 4, and by adhering to the static pressures shown below.

Note on chilled water

To avoid cavitation in chilled water circuits, please ensure sufficient counter pressure at valve outlet, e.g. by a throttling valve after the heat exchanger. Select the pressure drop across the valve at maximum according to the 80 °C curve in the flow diagram below.




- Δp_{max} = Differential pressure with valve almost closed, at which cavitation can largely be avoided
- p_1 = Static pressure at inlet
- p_3 = Static pressure at outlet
- M = Pump
- ϑ = Water temperature



Use the 3-port valve as a mixing valve.

Working pressure and medium temperature



Working pressure and medium temperature are according to ISO 7005

Current local legislation must be observed.

Notes

Engineering

We recommend installation in the return pipe, as the temperatures in this pipe are lower for applications in heating systems, which in turn, extends the stem sealing gland's life.

Ensure cavitation free flow, see page 6.

Warning



Always use a strainer upstream of the valve to increase the valve's functional safety.


Mounting

Both valve and actuator can easily be assembled at the mounting location. Neither special tools nor adjustments are required.


The valve is supplied with Mounting Instructions 74 319 0765 0.

Orientation

VVF47..



VXF47..



Direction of flow

When mounting, pay attention to the valve's flow direction symbol.

VVF47..

Through-port A to AB



VXF47..

Mixing A/B to AB



Commissioning



Commission the valve only if the actuator has been mounted correctly.

VVF47..

Valve stem retracts: valve opens = increasing volumetric flow
 Valve stem extends: valve closes = decreasing volumetric flow

VXF47..

Valve stem retracts: through-port A – AB opens, bypass B closes
 Valve stem extends: through-port A – AB closes, bypass B opens

Maintenance notes

Warning



V..F47.. valves require no maintenance.

When doing service work on the valve/actuator:

- Deactivate the pump and turn off the power supply
- Close the shutoff valves
- Fully reduce the pressure in the piping system and allow pipes to completely cool down

If necessary, disconnect the electrical wires.

Before putting the valve into operation again, make certain the actuator is correctly fitted.

Stem sealing gland

The glands cannot be exchanged at job site. Contact your local office or branch if the stem sealing gland range is damaged.

Disposal



Before disposal, the valve must be dismantled and separated into its various constituent materials.

Legislation may demand special handling of certain components, or it may be sensible from an ecological point of view.

Current local legislation must be observed.

Warranty


The technical data given for these applications is valid only in conjunction with the Siemens actuators. For details, please see page 2 "Equipment combinations". All terms of the warranty will be invalidated by the use of actuators from other manufacturers.

Technical data

Functional data	PN class	PN 16 to ISO 7268
	Working pressure	To ISO 7005 within the permissible "medium temperature" range according to the diagram on page 6.
	Flow characteristic	See section "Valve flow characteristic" on page 5.
	Leakage rate through-port bypass	0...0.1% of K_{vs} value 0.5...2% of K_{vs} value
	Permissible media	Chilled water, low temperature hot water, high temperature hot water, water with anti-freeze, brine; recommendation: water treatment to VDI 2035
	Medium temperature	1...95 °C
	Rangeability S_v	DN 50...150: > 50
	Nominal stroke	DN 50...80: 20 mm DN 100...150: 40 mm
Materials	Valve body	Grey cast iron EN-GJL-250
	Stem	Stainless steel
	Plug	Bronze or stainless steel
	Sealing gland	O-ring: EPDM; Wiper ring: PTFE
Dimensions/Weight	Refer to "Dimensions", page 10.	
	Flange connections	To ISO 7005
Environment	Operation	Class 3K5, 3Z11 Temperature -10...55 °C Rel. Humidity 5...95% r.h.
	Storage	Class 1K3 enhanced Temperature -15...50 °C Rel. Humidity <95% r.H.
	Transport	Class 2K3, 2M2 Temperature -30...+65 °C Rel. Humidity < 95% r.H.
	PN class	ISO 7268
	Working pressure	ISO 7005
	Flanges	ISO 7005
Norms	Length of flanged valves	DIN EN 558-1, Series 1
	Valve flow characteristic	VDI 2173
	Leakage rate	Throughport, bypass according to EN 60534-4 / EN 1349
	Water treatment	VDI 2035
	Environment	Storage: IEC 60721-3-1 Transport: IEC 60721-3-2 Operation: IEC 60721-3-3
	Environmental compatibility	ISO 14001 (Environment) ISO 9001 (Quality) SN 36350 (Environmentally compatible products) Directive 2002/95/EC (RoHS)

Dimensions (mm)


VVF47..



4419M06

	DN	B	Ø D	Ø D2	Ø D4	K	L1	L2	L3	H1	H2	H		Weight
												SBX..	SBV..	
												mm		
VVF47.50	50	20	165	19 (4x)	99	125	230	115	143	50	146	> 410	-	11.0
VVF47.65	65	20	185	19 (4x)	118	145	290	145	173	75	171	> 435	>500	16.0
VVF47.80	80	22	200	19 (8x)	132	160	310	155	185	75	171	> 435	>500	23.8
VVF47.100	100	24	220	19 (8x)	156	180	350	175	205	110	226	-	> 530	32.5
VVF47.125	125	26	250	19 (8x)	184	210	400	200	233	123	239		> 540	45.0
VVF47.150	150	26	285	23 (8x)	211	240	480	240	275	150	267		> 670	65.0

VXF47..



4419M07

	DN	B	Ø D	Ø D2	Ø D4	K	L1	L2	L3	H1	H2	H		Weight
												SBX..	SBV..	
mm														
VXF47.50	50	20	165	19 (4x)	99	125	230	115	115	50	146	> 410	-	8.7
VXF47.65	65	20	185	19 (4x)	118	145	290	145	145	75	171	> 435	>500	12.9
VXF47.80	80	22	200	19 (8x)	132	160	310	155	155	75	171	> 435	>500	19.5
VXF47.100	100	24	220	19 (8x)	156	180	350	175	175	110	226	-	> 530	27.7
VXF47.125	125	26	250	19 (8x)	184	210	400	200	200	123	239		> 540	38.3
VXF47.150	150	26	285	23 (8x)	211	240	480	240	240	150	267		> 570	54.1

DN = Nominal size

H = Total actuator height plus minimum distance to the wall or the ceiling for mounting, connection, operation, maintenance etc.

H1 = Dimension from the pipe centre to install the actuator (upper edge)

H2 = Valve in the "Closed" position means that the stem is fully extended

Revision number

Product number	Valid from rev. number	Product number	Valid from rev. number
VVF47.50	..B	VXF47.50	..B
VVF47.65	..B	VXF47.65	..B
VVF47.80	..B	VXF47.80	..B
VVF47.100	..C	VXF47.100	..B
VVF47.125	..C	VXF47.125	..B
VVF47.150	..C	VXF47.150	..B

Issued by
Beijing Siemens Cerberus Electronics Ltd.
Smart Infrastructure

© Beijing Siemens Cerberus Electronics Ltd., 2024
Technical specifications and availability subject to change without notice.

No.1, Fengzhi East Road, Xibeiwang
Haidian District, 100094 BEIJING, China
+86 10 64768806
www.siemens.com/buildingtechnologies