October 12, 2023

SIEMENS

Series QAA2200 Room Temperature Sensors & Series QFA3200 Room Humidity Sensors



QxAx2xx.EWSN Sensing Only



QxAx2xx.FWSN Full HMI

Description

Series QAA2200 Room Temperature and Series QFA3200 Room Humidity + Temperature sensors are engineered to enable accurate and efficient control of room comfort. A wide variety of output signals is available for compatibly with nearly any control system. The patented housing design seamlessly blends into any décor and features strategically placed ventilation slots to maximize airflow and optimize accuracy.

The QFA3200 units combine a temperature sensor with a relative humidity sensor in a single housing to reduce installation time and improve overall room aesthetics.

Installation is quick and straightforward with all hardware included for mounting on a standard 2" x 4" electrical box. Screws and anchors are provided for mounting the sensor directly to a wall. Matching gaskets and trim rings are also available.

The "E" versions have a blank front to prevent unauthorized adjustments and are ideal for high traffic areas or remote spaces that are not supervised.

The "F" versions feature a full HMI that can display room conditions and temperature setpoint. The display is easily configured to limit the information that is available to the occupant. Temperature setpoint can be adjusted using soft touch plus (+) and minus (-) keys, and an override key enables the user to manually signal to the controller that the space is occupied.

Specifications

opoonioanono	
Temperature	
Measuring range	32°F to 122°F (0°C to 50°C)
Accuracy	
1K Ω Pt	± 0.54°F (0.3°C) @ 32°F (0°C)
1K Ω (32°F) Ni	± 0.72°F (0.4°C) @ 32°F (0°C)
10K Ω Type II	± 0.4°F (0.22°C) @ 77°F (25°C)
100K Ω Type II	± 0.36°F (0.2°C) @ 77°F (25°C)
4 to 20 mA/0 to 10V	± 0.9°F (0.5°C)
Humidity	
(QFA32xx only)	
Measuring Range	0 to 100% rh
Accuracy	± 2% between 10 to 90%
Long-Term Stability	<0.5% rh/year
Resolution	0.03% rh
Repeatability	+/-0.1% rh
Setpoint/Override	_
("F" versions only)	
Setpoint Signal	
QxAx2 SS .FWSN	4 to 20 mA or 0 to 10V/0 to 5V
All others	0 to 10V/0 to 5V
Setpoint Range	55°F to 95°F (13°C to 35°C)
Override Contact	Momentary, 1A @ 24 Vac max.
Input Power	18 to 36 Vdc or 24 Vac ± 20%
VA Rating	1.5 VA, max.
Agency Listing	UL 916
-	CSA C22.2 No. 205
Color	White
Dimensions	4.5" × 2.75" × 1.18"
	$(115 \text{ mm} \times 70 \text{ mm} \times 30 \text{ mm})$
Shipping Weight	6 oz. (170 g)

Siemens Industry, Inc. Page 1 of 2

Product Ordering Information

Part Number ¹	Temperature Output	Humidity Output	Display	Setpoint Adjustment
QAA2212.EWSN	Dt 414 O (205-) DTD		_	_
QAA2212.FWSN	Pt 1K Ω (385a) RTD		•	•
QAA2220.EWSN	N: 41/ O @ 22%F DTD		_	_
QAA2220.FWSN	Ni 1K Ω @ 32°F RTD		•	•
QAA2230.EWSC ²			_	_
QAA2230.EWSN	40K O Tura II Thermister	_		
QAA2230.FWSC ²	10K Ω Type II Thermistor		•	•
QAA2230.FWSN				
QAA2235.EWSN	100K $Ω$ Type 2 Thermistor		_	_
QAA22SS.EWSN	0 to 10V/4 to 20 mA			
QAA22SS.FWSN	(Selectable)		•	•
QFA3212.EWSN	D(4K O (2005 -) DTD		_	_
QFA3212.FWSN	Pt 1K Ω (385a) RTD	4 - 20 mA or	•	•
QFA3230.FWSN	10K Ω Type II Thermistor	0 - 10V/		
QFA32SS.EWSN	0.45.40\//4.45.20=4	0 - 5V (Selectable)	_	_
QFA32SS.FWSN	0 to 10V/4 to 20mA	(Scicolable)	•	•

¹For no-logo version, change "S" to "N" in Part Number position 10.

Accessories Ordering Information

Description	Part Number
Room Unit Back Plate (10-pack)*	AQA2200-INTL
Room Unit Back Plate (Single)*	AQA2200-2X4
Room Sensor Insulating Gasket (10-pack) (Recommended for hollow wall installations.)	563-102 GSKT KIT

^{*} For use when installing Series 2200/3200 Sensors on conduit boxes other than U.S. style 2" x 4". Back plate measures 3-1/4" x 5" (82.55 mm x 127 mm).

Disposal



The devices are considered electrical and electronic equipment for disposal in terms of the applicable European Directive and may not be disposed of as domestic garbage.

- Dispose of the devices through channels provided for this purpose.
- Comply with all local and currently applicable laws and regulations.

Information in this document is based on specifications believed correct at the time of publication. The right is reserved to make changes as design improvements are introduced. Product or company names mentioned herein may be the trademarks of their respective owners. © 2018-2023 Siemens Industry, Inc.

²For use with TALON[®] LON controllers.